






PRODUCT NO.
10147430-1X3T0LF




SECTION A-A





spec ref -				dr Noorhazelinda, 2018/09/20		projection	mm	size A3	scale 1:1
tolerance std ISO 406 ISO 1101 TOLERANCES UNLESS OTHERWISE SPECIFIED				eng Sandar Soe 2021/05/18				ecn no ELX-S-39084-1	
				chr - -					
				appr Koon-Poh Tay 2021/05/21					product family -
surface ISO 1302 ✓	linear	0.X	±0.3	Amphenol FCI	title PCIE GEN4, SMT, LATCH MODULE ASSY - BLADE HOLDDOWN	dwg no 10147430	rev C		
		0.XX	±0.20						
		0.XXX	±0.10						
	angular	0°	±2°					cat. no. -	Product - Customer Drw





RECOMMENDED PCB LAYOUT, PAD TYPE

DIMENSIONS			
POSITION	A	B	C ±0.10
164	70.00	71.65	73.15

spec ref -				dr	Noorhazinda,	2018/09/20	projection 	mm 	size	A3	scale	1:1					
tolerance std				eng	Sandar Soe	2021/05/18			ecn no				ELX-S-39084-1				
ISO 406				chr	-	-			rel level				Released				
ISO 1101				appr		Koon-Poh Tay			2021/05/21	product family							
surface	linear	0.X	±0.3	Amphenol FCI	title				PCIE GEN4, SMT, LATCH				dwg no	10147430		rev	C
		0.XX	±0.20														
		0.XXX	±0.10														
	ISO 1302	angular	0°	±2°	cat. no.		Product - Customer Drw				sheet 3 of 4						

PRODUCT NUMBER CODE

10147430-□□□□LF

HOUSING
I: BLACK

CONTACT AREA PLATING
1: 30u" Au
2: 15u" Au


LATCH OPTIONS
0: LATCH COLOR: BLACK
I: WITHOUT LATCH

PACKAGING OPTIONS
T: SOFT TRAY WITH KAPTON TAPE, 22MM
V: SOFT TRAY WITH KATPON TAPE, 86.5MM
Q: SMALL HARD TRAY (323x136MM) WITHOUT KAPTON TAPE
A: SMALL HARD TRAY (323x136MM) WITH KAPTON TAPE, 22MM
K: CUSTOM HARD TRAY (295X185MM) WITHOUT KAPTON TAPE
L: CUSTOM HARD TRAY (295X185MM) WITH KAPTON TAPE, 22MM

NO. OF POSITION
3: 164 POSITION

NOTES:

- 1. MATERIAL :
HOUSING : LCP, UL94V-0
LATCH : LCP, UL94V-0
CONTACT COPPER ALLOY
HOLDDOWN CLIP: COPPER ALLOY
- 2. PLATING:
CONTACT: UNDERPLATE: 50u" NICKEL OVERALL.
SOLDER AREA: 100u" TIN (LEAD FREE).
MATING AREA: SEE PRODUCT NUMBER CODE.
HOLDDOWN CLIP: 100u" TIN OVER 50u" NICKEL.
- 3. PRODUCT SPECIFICATION: GS-12-1406
- 4. PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004
- 5. DATE CODE "MMDDYYL", MMDDYY IS ASSEMBLY DATE.
L IS AFCI PRODUCTION SITE.
- 6. THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- 7. A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.



DIMENSIONS	
KAPTON TAPE LENGTH	(Dim M)
22MM	33.5
86.5MM	1.25

spec ref		-		dr	Noorhazinda,	2018/09/20			size	A3	scale	1:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Sandar Soe	2021/05/18			ecn no	ELX-S-39084-1		
ISO 406 ISO 1101				chr	-	-			rel level	Released		
				appr	Koon-Poh Tay	2021/05/21	product family		-			
surface 	linear	0.X	±0.3	Amphenol FCi	title PCIE GEN4, SMT, LATCH MODULE ASSY - BLADE HOLDDOWN			dwg no	10147430			rev C
		0.XX	±0.20									
		0.XXX	±0.10									
ISO 1302	angular	0°	±2°		cat. no.		-	Product - Customer Drw			sheet 4 of 4	