Thomas&Betts

Catalog Number: **HSB46**
Product ID: 7TCA017300R0352
UPC Number: 78621053473
EAN Number: 05414363104322
Status: A



Actual

Thin Wall Heat Shrink Tubing in Dispenser Box - 3/64 Inch Expanded Inside Diameter - 12.0 Meters, Black, Shrink Ratio 2:1, CrossLinked Polyolefin, Item is Silicone, Cadmium and Lead Free

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Shrink Ratio	2:1
Thickness	Thin
Length	39.37 in ; 12 m
Dielectric Strength	280 V/Mil (11kV/mm)
Continuous Operating Temperature	-67 to +212 F ; -55 to +100 C
Minimum Shrink Temperature	230 F ; 110 C
Flammability	Self Extinguishing
Water Absorption	0.03%
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	1.2mm
Inner diameter after heat-shrink	0.6mm
Nominal diameter inch	3/64 inch
Wall thickness after shrinking	0.4mm
Length	12m
Operation temperature	-55-+135°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	N

Packaging

Inner Quantity	1
Inner Dimensions (inches)	6.7x2.4x6.7
Outer Quantity	60
Outer Dimensions (inches)	20.9x15.8x22.5
Weight Uom	27.6 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001466
Catalog	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

Downloaded from Arrow.com.

www.tnb.com Memphis, TN 38120 Fax: (901) 252-1321
Email:techsupport@tnb.com

Downloaded from Arrow.com.