


Part Number : [1511300001](#)

Product Description : Block-Style SIM Connector, 0.38mm Height, Surface Mount, 0.38µm Gold (Au) Plating, 6 Circuits

Series Number : 151130

Status : Obsolete


Product Category : Memory / SIM Card Connectors



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Memory / SIM Card Connectors
Series	151130
Description	Block-Style SIM Connector, 0.38mm Height, Surface Mount, 0.38µm Gold (Au) Plating, 6 Circuits
Product Name	Block SIM
Style	Block
UPC	889056217620

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	10V DC

Physical

Card Detection Switch	No
Card Entry Location	Front
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	1500
Ejector Button Side	N/A
Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	0.054/g
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.54mm

Pitch - Termination Interface	2.54mm
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	SIM Card

This document was generated on May 08, 2026

Obsolete