TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

TERMINALS & SPLICES

CRIMP WIRE PINS, TABS & FERRULES



✔ Active

TE CONNECTIVITY (TE)

PIDG WIRE PIN

PIDG

165133
TE Internal Number: 165133

EU RoHS Compliant
EU ELV Compliant

Terminal Type Wire Pin

Wire Insulation Diameter (Max) 7.62 mm [.3 in]

Wire Insulation Diameter (in) .17 – .3

Heavy Duty No

Wire Size (AWG) 12 – 10

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

WIRE PIN PIDG

PDF **(TIFF AVAILABLE)**

English

Agency Approvals

CSA Certificate

PLASTI-GRIP INSULATED BUTT SPLICES, TERMNAL SPLICES AND TERMINALS REPORT

PDF

English

FEATURES

Downloaded from Arrow.com.

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Barrel Type Closed Barrel
Wire/Cable Type Regular Wire
Insulated Yes
Insulated Wire Support Yes
Support Style Insulation Support

Body Features

Insulation Color Yellow
Plating Material Copper, Tin
Insulation Material Nylon
Double Wire No
Sleeve Material Copper

Contact Features

Terminal Type Wire Pin
Terminal Orientation Straight
Terminal Length 9.9 mm [.39 in]

Termination Features

Bullet Terminal Without

Dimensions

Wire Insulation Diameter (Max) 7.62 mm [.3 in]
Wire Insulation Diameter (in) .17 – .3
Wire Size (AWG) 12 – 10
Wire Size (mm^2) 3 – 6
Wire Size (CMA) 5180 – 13100
Barrel Inside Diameter 8 mm [.315 in]
Overall Length 31.3 mm [1.232 in]

Operation/Application

Heavy Duty No

Packaging Features

Packaging Method Box
Packaging Quantity 500

Other

Barrel Color Yellow

PRODUCT COMPLIANCE

Statement of Compliance

Downloaded from Arrow.com.

Statement of Compliance

PDF

Downloaded from Arrow.com.