



Home> Products > Cermet and Wirewound Elements> 58 > Product Page

58C120K



Actual product appearance may vary.

58 Series Industrial Potentiometer, Wire Wound Element, Solder lug Terminals, 4 W Power Rating, 20 kOhm Resistance Value

Features

- Robust nickel-plated brass shaft and bushings
- Wirewound element
- Linear taper
- Very stable over the operating temperature

Potential Applications

- Manual controls
- Welding and heating

Description

The 58 Series is a 4 watt potentiometer made with a wirewound element. It offers a rugged metal construction and a linear taper.

Supporting Documentation

 [Dimensions](#)

Product Specifications		
Potentiometer Type	Industrial	
Element Type	Wire Wound	
Terminal Type	Solder lug	
Power Rating	4 W	
Resistance Value	20 kOhm	
Resistance Tolerance	± 5 %	
Linearity	± 2 %	
Bushing Thread	9,53 mm [0.375 in] x 32 NEF	- 2A
Bushing length	9,53 mm [0.375 in]	
Bushing Type	Standard	
Shaft Diameter	6,35 mm [0.25 in]	
Shaft length	50,80 mm [2.0 in]	
Shaft Ending	Plain round	
Body	42.93 mm [1.69 in] diameter, ± 0.79 mm [0.031 in], except at terminal standoff	
Electrical Taper	Linear	
Operating Temperature	- 55 °C to 105 °C [- 67 °F to 220 ° F]	
Working Voltage (Max.)	350 V	
Rotational Life	25000 cycles	
Mechanical Rotation	300°	
Availability	Global	
Series Name	58	
UNSPSC Code	4111363300	
UNSPSC Commodity	4111363300 Potentiometers	

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search