



CPH5505

Bipolar Transistor -30V, -3A, Low $V_{CE(sat)}$, PNP Dual CPH5

ON Semiconductor®

<http://onsemi.com>

Applications

- Relay drivers, lamp drivers, motor drivers, flash

Features

- Composite type with two PNP transistors contained in a single package facilitating high-density mounting
- The CPH5505 consists of two chips which are equivalent to the CPH3109 encapsulated in a package
- Ultrasmall package facilitates miniaturization in end products (mounting height : 0.9mm)

Specifications

Absolute Maximum Ratings at $T_a=25^\circ\text{C}$


Parameter	Symbol	Conditions	Ratings	Unit
Collector to Base Voltage	V_{CBO}		-30	V
Collector to Emitter Voltage	V_{CEO}		-30	V
Emitter to Base Voltage	V_{EBO}		-5	V
Collector Current	I_C		-3	A
Collector Current (Pulse)	I_{CP}		-5	A
Base Current	I_B		-600	mA
Collector Dissipation	P_C	When mounted on ceramic substrate (600mm ² ×0.8mm)	0.9	W
Total Dissipation	P_T	When mounted on ceramic substrate (600mm ² ×0.8mm)	1.2	W
Junction Temperature	T_J		150	°C
Storage Temperature	T_{stg}		-55 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Package Dimensions

unit : mm (typ)


7017A-009




Product & Package Information

- Package : CPH5
- JEITA, JEDEC : SC-74A, SOT-25
- Minimum Packing Quantity : 3,000 pcs./reel


Packing Type : TL



Marking



Electrical Connection




CPH5505

Electrical Characteristics at Ta=25°C









Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Collector Cutoff Current	ICBO	VCB= -30V, IE=0A			-0.1	μA
Emitter Cutoff Current	IEBO	VEB= -4V, IC=0A			-0.1	μA
DC Current Gain	hFE	VCE= -2V, IC= -500mA	200		560	
Gain-Bandwidth Product	fT	VCE= -10V, IC= -500mA		380		MHz
Output Capacitance	Cob	VCB= -10V, f=1MHz		25		pF
Collector to Emitter Saturation Voltage	VCE(sat)1	IC= -1.5A, IB= -30mA		-155	-230	mV
	VCE(sat)2	IC= -1.5A, IB= -75mA		-105	-155	mV
Base to Emitter Saturation Voltage	VBE(sat)	IC= -1.5A, IB= -30mA		-0.83	-1.2	V
Collector to Base Breakdown Voltage	V(BR)CBO	IC= -10μA, IE=0A	-30			V
Collector to Emitter Breakdown Voltage	V(BR)CEO	IC= -1mA, RBE=∞	-30			V
Emitter to Base Breakdown Voltage	V(BR)EBO	IE= -10μA, IC=0A	-5			V
Turn-ON Time	ton	See specified Test Circuit.		50		ns
Storage Time	tstg			270		ns
Turn-OFF Time	tff			25		ns




Switching Time Test Circuit




Ordering Information

Device	Package	Shipping	memo
CPH5505-TL-E	CPH5	3,000pcs./reel	Pb Free






Outline Drawing
CPH5505-TL-E



Land Pattern Example



ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.