



Products

Self-Adjusting Crimping Pliers for End Sleeves (ferrules), with front loading

patented

97 53 08



0,08 - 10,0 mm²

square crimp

97 53 09



0,08 - 10,0
+ 16 mm²

square crimp

Info Special Applications

- for crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4
- for solder-free electrical connections
- front loading of the end sleeves (ferrules) into the tool
- simple handling as a result of self-adjustment to the size of the end sleeve (ferrule)
- with square crimping for optimum contact areas in the clamp connection
- repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- these tools have been set precisely (calibrated) in the factory
- optimum transmission of force due to lever action for fatigue-reduced operation
- high operation comfort thanks to handy shape and low weight
- all stressed parts are made of special steel, oil-hardened and tempered

Model: 97 53 08

- crimping from 0.08 - 10.0 mm² in one profile
- end sleeves (ferrules) up to 2.5 mm² can also be loaded parallelly from the side

Model: 97 53 09

- crimping from 0.08 - 10.0 and 16.0 mm² in one profile
- with selector lever for setting the crimping area either to 0.08 - 10 mm² or 16 mm²

Article-No.	EAN 4003773-	Head	Handles	Symbols	Range of Application	Capacity mm ²	Capacity AWG	Length mm	g	
97 53 08	040187	burnished	with two-colour dual component handles		End Sleeves (ferrules)	0,08 - 10,0	28 - 7	190	490	
97 53 09	044550	burnished	with two-colour dual component handles		End Sleeves (ferrules)	0,08 - 10 + 16	28 - 7 + 5	190	460	

technical change and errors excepted

