



CONNECTORS

TERMINAL BLOCK HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)

PWR TB DBL PIN 7P, 15.00 PCB

Buchanan

1986713-7

TE Internal Number: 1986713-7

EU RoHS Compliant

EU ELV Compliant

Connector Style Receptacle

Number of Positions 7

Centerline (Pitch) 15 mm [.591 in]

Number of Rows 1

Wire Entry Angle Side

 **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

POWER TERMINAL BLOCK, SOLDERABLE UP TO 275DEG C DOUBLE PIN MODULAR 02 - 12 POLES

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Shrouded No
Block Type Straight
Connector Style Receptacle
Connector & Contact Terminates To Printed Circuit Board

Configuration Features

Number of Positions 7
Number of Rows 1
Wire Entry Angle Side
Side Stackable Yes
Threaded Flange Without

Electrical Characteristics

Voltage (VAC) 600

Body Features

Interlock Without

Contact Features

Pin Length 5 mm [.197 in]
Contact Mount Through Hole
Contact Base Material Copper Alloy
Contact Mating Area Plating Material Tin

Mechanical Attachment

Screw Flange Without
Screw Material Steel
Screw Plating Material Nickel
Screw Size M5
Mounting Angle Vertical
Screwless Terminal Block No

Housing Features

Centerline (Pitch) 15 mm [.591 in]
Housing Material Polyamide
Housing Color Green

Dimensions

Wire Range .5 – 41 mm² [20 – 1 AWG]
PCB Tail Length 5 mm [.196 in]

Packaging Features

Packaging Quantity 5
Packaging Method Carton

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
