




Part Number : [2125700100](#)

Product Description : 824MHz-2170MHz Side-Fed Cellular Flexible Antenna, 100.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

Series Number : 212570

Status : Active

Product Category : Antennas



Documents and Resources

Drawings

[2125700100_sd.pdf](#)

[2125700100-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[2125700100-000.pdf](#)

[2125700100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	212570
Description	824MHz-2170MHz Side-Fed Cellular Flexible Antenna, 100.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	Side-Fed Cellular Flexible
Protocol	Cellular
Type	Cellular Antenna, Internal
UPC	193264168675

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	824
Band#2 F_End (MHz)	2170
Band#2 F_Start (MHz)	1710
Electrical Connectivity	Cable
Peak Gain (dBi)	-0.45 @ 824 MHz, 1.76 @ 1710

	MHz
Return Loss - S11 (dB)	< -3, < -4
Total Efficiency	>25% @ 824 MHz, >50% @ 1710 MHz

Physical

Cable Length	100.00mm
Length	40.40mm
Mounting Style	Adhesive
Net Weight	0.744/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	15.40mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	<u>734120110</u>

This document was generated on Apr 15, 2026