

High Efficiency · Stability · Energy Saving

PRODUCT

[New Products](#) | [Products Overview](#) |

[Home](#) > [Products](#) > [New Products](#)

New Products

Products

- > AC Redundant Module
- > DC Redundant Module
- > 1U Redundant
- > 2U Redundant
- > 3U Redundant
- > Mini Redundant
- > 1U Standalone
- > 2U Standalone
- > PS2
- > PoE

AC Redundant Module 150 watts



YM-2151EAR

FEATURES

- 150.0 (L) x 50.5 (W) x 40.0 (H) mm
- N+1 Redundant
- Support PMBus 1.2
- No Minimum Load Required
- Application for IPC/Storage/Embedded server/Networking



Download

[Print](#) | [Drawing](#) | [BSMI](#) | [CB](#) | [CCC](#) | [CE](#) | [FCC](#) | [TUV](#) | [UL](#)



INPUT

Input Voltage	90-264VAC
Input Frequency	47-63Hz
Input Current	3.0A max at 115VAC, 1.5A max at 230VAC
Inrush Current	25A max at 90 - 264VAC
Power Factor	0.98 at 115VAC / 60Hz, 0.94 at 230VAC / 50Hz
Earth Leakage Current	1.5mA max at 240VAC / 50Hz

GENERAL


Efficiency	80 Plus SILVER certified, Highest efficiency
Power Density	89% at 230VAC
MTBF	8.11 W/in ³ 100 khrs per Bellcore SR-332 ISSUE1 at 25°C ambient

ENVIRONMENTAL

Operating Temperature	-5 to 50°C
Operating Humidity	85% RH, Non-condensing
Storage Temperature	-40°C to +70 °C
Operating Altitude	Sea level to 5,000 M
Shock Operating	10G, no malfunction
Non-Operating	0.02G ² /Hz form 20Hz to 1kHz
Vibration Operating	0.01G ² /Hz at 10Hz, 0.02G ² /Hz at 20Hz

EMC & SAFETY

Emissions	EN55022, class B Conducted EN55022, class B Radiated
Harmonic Currents	EN61000-3-2
Voltage Flicker	EN61000-3-3
EFT/Burst	EN61000-4-4
Surge	EN61000-4-5
Conducted Immunity	EN61000-4-6
Safety Approvals	UL/cUL, TUV, CB, CE, CCC, FCC



Output	Minimum Load	Maximum Load	Condition	Ripple & Noise
--------	--------------	--------------	-----------	----------------

	+12V	0A	12.5A		120mV p-p
	+5VSB	0A	3.0A		50mV p-p

Taiwan Headquarters

TEL :+886-3-321-4556 FAX :+886-3-321-4576 E-mail :3ysales@3ypower.com.tw
Address : 2nd Fr, No. 576, Sec. 1, Minsheng N. Rd., Gueishan, Taoyuan, Taiwan 333, R.O.C.

Site Map

Copyright© 3Y Power Technology Inc. All Right Reserved.