

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-20-004655	29SEP2020	RK	SBH

D

C

B

A




D

C


B

A

LV-2




LV-2



1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO
TE-SPEC.108-18857, SUBSECTION 3.1.1

3 WIRING SCHEDULE AS SHOWN

WIRING SCHEDULE			
OUTLET		SIDE	PLUG
1	+	RIBBED	1
2	-	SMOOTH	2



OBSOLETE	16.0 FT	±3.84	2181192-8
	14.0 FT	±3.36	2181192-7
	12.0 FT	±2.88	2181192-6
	10.0 FT	±2.4	2181192-5
OBSOLETE	8.0 FT	±1.92	2181192-4
	6.0 FT	±1.44	2181192-3
	4.0 FT	±.96	2181192-2
	2.0 FT	±.48	2181192-1
	"L"	TOLERANCES [INCHES]	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 16/JUN/11		 TE Connectivity			
		CHK P. BECKER 13/JUL/11					
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME CABLE ASSEMBLY, NECTOR, LV-2, OUTLET TO PLUG			
		APVD P. BECKER 01/AUG11					
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		SIZE A2					
		CAGE CODE 00779					
MATERIAL —		FINISH —		DRAWING NO C=2181192		RESTRICTED TO —	
		WEIGHT —		SCALE N.T.S.		SHEET 1 of 1	
		CUSTOMER DRAWING		REV A1			

2181192