

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
(C) COPYRIGHT - By - ALL RIGHTS RESERVED.			
PROJECT	PRJ-16-000909157		
PART NO.	X-2308319-X		
DESCRIPTION	FULL METAL HOODS SIZE 1		
CUSTOMER	GENERAL MARKET		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED PER ECR-16-014891	20OCT2016	KK	GG
	A3	ECR-22-139688,CORRECT ERROR	19MAY2022	TF	CW

NOTES:

1. TEMPERATURE: -40°C TO $+90^{\circ}\text{C}$.
2. STRAND DIAMETER OF CRIMP FLANGE: 2.7–8.7 mm.
3. CABLE DIAMETER WITH EXTERNAL CABLE CLAMP: 4–14 mm.
4. CABLE DIAMETER WITH INTERNAL CABLE CLAMP: $d=4\text{--}10$ mm
(FOR $d=4\text{--}7$ mm TURN CABLE CLAMP).
5. CABLE BUSHING FOR CABLE DIAMETER 4–9 mm.


* CRIMP FLANGE PN *-2308349-* TO BE ORDERED SEPARATELY.





* CRIMP BARREL TO BE USED IN COMBINATION WITH THE FLANGE PN *-2308350-* TO BE ORDERED SEPARATELY.

* CABLE CLAMP SCREW VERSION PN *-2308272-* TO BE ORDERED SEPARATELY.



1-2308319-5	FULL METAL HOOD1 5	HOUSING 2	—	2	2	3	53
1-2308319-4	FULL METAL HOOD1 4	HOUSING 2	1	1	1	2	55
1-2308319-3	FULL METAL HOOD1 3	HOUSING 2	—	2	—	3	51
1-2308319-2	FULL METAL HOOD1 2	HOUSING 2	1	1	—	2	53
1-2308319-1	FULL METAL HOOD1 1	HOUSING 1	1	—	—	—	49
ASSY. PART NO.	DESCRIPTION	SUB-PART DESCRIPTION POS.1	POS.3	POS.5	POS.6	POS.7	WEIGHT, g
	DESCRIPTION						

9	1	—	SCREW M2.5x5 (CASE HARDENING STEEL, ZINC-PLATED)
8	4	—	SCREW M2.5x6.5 (CASE HARDENING STEEL, ZINC-PLATED)
7	SEE TAB. POS.7	—	SCREW M2.5x6 (CASE HARDENING STEEL, ZINC-PLATED)
6	SEE TAB. POS.6	—	CABLE BUSHING (EPTR SANTOPRENE)
5	SEE TAB. POS.5	—	CABLE CLAMP (BAND STEEL, ZINC-PLATED)
4	2	—	CATCH SPRING (STAINLESS STEEL, RAW)
3	SEE TAB. POS.3	—	BLIND PLATE (ZINC ALLOY, RAW)
2	1	—	COVER (ZINC ALLOY, RAW)
1	1	SEE TAB. POS.1	HOUSING (ZINC ALLOY, RAW)
SL NO.	QTY	PART NO.	DESCRIPTION (MATERIAL, FINISH)


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN K03AUG2016		TE Connectivity									
DIMENSIONS: mm		CHK GUNASEKHAR G03AUG2016											
		APVD GUNASEKHAR G03AUG2016		NAME FULL METAL HOODS SIZE 1									
		PRODUCT SPEC —											
		APPLICATION SPEC —											
		—											
TOLERANCES, UNLESS OTHERWISE SPECIFIED: DIN ISO 2768 m		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		WEIGHT		A200779		C=2308319		—					
MATERIAL —		FINISH —		CUSTOMER DRAWING				SCALE NTS		SHEET 1 OF 1		REV A3	



CRIMP FLANGE



CRIMP BARREL



CABLE CLAMP

