


Data Sheet | Item Number: 216-144

Ferrule; Sleeve for 1.5 mm² / AWG 16; uninsulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 1/08.92; silver-colored

<https://www.wago.com/216-144>



Color: ■ silver-colored

Similar to illustration

Dimensions in mm

Connection Data		
Metric cross-section of the ferrule		1.5 mm ²
Strip length		10 mm / 0.39 inches
Cross-section (AWG) of ferrule		16 AWG

Physical data		
Total length (L)		10 mm
Wall thickness of crimp sleeve (W2)		0.15 mm
Diameter crimp sleeve inside (D2)		1.7 mm

Mechanical data		
Plastic collar		No

Material data		
Color		silver-colored
Weight		0.1 g

Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		5000 (1000) pcs
Packaging type		Box
Country of origin		DE
GTIN		4044918016384
Customs tariff number		85369010000



Product Classification	
UNSPSC	39121405
eCl@ss 10.0	27-40-02-01
eCl@ss 9.0	27-40-02-01
ETIM 9.0	EC000005
ETIM 10.0	EC000005
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance


Compliance Search

Environmental Product Compliance 216-144

↓

Documentation			
Bid Text			
216-144	19.02.2019	xml 2.87 KB	↓
216-144	13.06.2017	doc 23.00 KB	↓

Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable