

SE Series



Agency Approvals

AGENCY	AGENCY FILE NUMBER
	E128662

2 Electrode GDT Graphical Symbol



Additional Information



Datasheet



Resources



Samples

Description

Littelfuse SE series GDT offers high surge ratings in a miniature package. It's designed for surface mounting on PCB with small size 3.2x1.6x1.6mm. Low insertion loss is perfectly suited to broadband equipment applications. The capacitance does not vary with voltage, and will not cause operational problems with ADSL2+, where capacitance variation across Tip and Ring is undesirable. These devices are extremely robust and are able to divert a 500A-600A pulse in a miniature package 1206 without destruction.

Features

- RoHS compliant and Lead-free
- GHz working frequency
- Excellent stability on multiple pulse duty cycle
- Excellent response to fast rising transients.
- Ultra Low Insertion Loss
- 0.5-0.6KA surge capability tested with 8/20μS pulse as defined by IEC 61000-4-5
- Ultra small devices offered in a variety of mounting lead forms
- Non-Radioactive
- Low capacitance (<0.5pF)
- Voltage Ranges 140V to 500V
- UL recognized
- Conforms to ITU-T K12, IEC 1000-4-5
- Square Outline

Applications

- Communication equipment
- CATV equipment
- Test equipment
- Data lines
- Power supplies
- Telecom SLIC protection
- Broadband equipment
- ADSL equipment, including ADSL2+
- XDSL equipment
- Satellite and CATV equipment
- General telecom equipment

Part Number	Device Specifications (at 25°C)										Life Ratings	
	DC Breakdown in Volts (@100V/s)			Impulse Breakdown in Volts (@100V/μs)	Impulse Breakdown In Volts (@1 Kv/μsec)	Insulation Resistance	Capacitance (@1MHz)	Arc Voltage (@1A)	Glow to Arc Transition Current	Glow Voltage	Nominal Impulse Discharge Current (x10 @8/20μs)	Nominal Impulse Discharge Current (x10 @5/320μs)
	MIN	TY	MAX	MAX		MIN	MAX					
	SE140	98	140	182	800	900	>1GΩ (at 100VDC)	<0.5 pf	~10 V	<1.0 A	~60 V	0.5 kA
SE200	140	200	260	700	1100	<0.3 pf		<1.0 A				
SE230	172	230	276	600	800	<0.5 pf		<1.0 A				
SE350	265	350	495	900	1150	<0.5 pf		<1.0 A				
SE470	329	470	611	1050	1200	<0.3 pf		<1.0 A		0.5 kA		
SE500	400	500	600	1050	1200	<0.3 pf		<1.0 A		0.5 kA		

Materials	Device Tin Plated 17.5±12.5 Microns Construction Ceramic Insulator.
Storage and Operational Temperature	-40 to +90 °C

The graph illustrates the voltage characteristics of a thyristor during its turn-on process. The y-axis represents Voltage (V) and the x-axis represents Time (ns). The curve starts at (0,0), rises to a peak labeled 'Max dynamic breakover voltage' at approximately 500ns, then drops to a level labeled 'Hold-over voltage' and remains constant until about 600ns, after which it drops further to a level labeled 'On-State voltage'.

Tape Specifications


IEC 60286-3
Dimensions in mm

The drawing illustrates the specifications for SMD-Tape, showing dimensions in mm. Key features include:

- Top View:** Shows a series of pockets with a width of 1.9 ± 0.1 mm and a pitch of 4 ± 0.1 mm. The total width is 12 ± 0.3 mm. The distance from the edge to the first pocket is 5.6 ± 0.1 mm. The distance between the center of two pockets is 4 ± 0.1 mm. The distance from the center of a pocket to the edge is 1.75 ± 0.1 mm. The distance from the center of a pocket to the next pocket is 2 ± 0.1 mm. The distance from the center of a pocket to the edge is 1.5 ± 0.05 mm. The distance from the center of a pocket to the edge is 1.5 ± 0.05 mm.
- Side View (Section A-A):** Shows the profile of the tape with a thickness of 0.4 ± 0.05 mm and a lead-in length of 3.7 ± 0.1 mm. The lead-in is bent at an angle of 5° .
- End View (Section B-B):** Shows the profile of the tape with a width of 2.1 ± 0.1 mm and a lead-in length of 5° .


SMD-Tape has to withstand a minimum Force of $F > 20 \text{ N}$ / pocket
2 Kg / pocket
minimum vertical load (minimum checking quantity: 10 pockets)

IEC 60286-3
Dimensions in mm




Soldering Parameters - Reflow Soldering (Surface Mount Devices)

Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (Min to Max) (t_s)	60 – 180 secs
Average ramp up rate (Liquidus Temp (T_L) to peak		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		5°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Temperature (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		10 – 30 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		260°C



Device Dimensions



Part Numbering System and Ordering Information

SE xxx

Series ———

1206 Square GDT

Breakdown Voltage ———

140 = 140V
200 = 200V
230 = 230V
350 = 350V
470 = 470V
500 = 500V

Packaging

Part Number	Packaging Option	Quantity
SE140	Tape and Reel	3,000
SE200	Tape and Reel	3,000
SE230	Tape and Reel	3,000
SE350	Tape and Reel	3,000
SE470	Tape and Reel	3,000
SE500	Tape and Reel	3,000