

## SmartRack Standard Sliding Shelf (50 lbs / 22.7 kgs capacity; 28.3 in/719 mm Deep)

MODEL NUMBER: SRSHELF4PSL



### Highlights

- Sliding Shelf mountable rack accessory
- Designed for 4 post rack mounting
- 28.3 in. / 72cm shelf depth, supports up to 50 lbs (22.7 kgs)
- Extendable shelf accommodates tower units, monitors, and other equipment
- Cold rolled steel with black finish
- Required mounting hardware included

### Package Includes

- Shelf
- Mounting hardware

### Description

SmartRack® SRSHELF4PSL is a standard sliding shelf for installation in rack cabinets. The SRSHELF4PSL has a 28.3-inch (720 millimeters) depth (29.5 inches including handle) and can support up to 50 pounds (22.7 kilograms). This extendable shelf can accommodate tower units, monitors and other equipment. It is designed for 4-post rack-mounting and the required mounting hardware is included. Expandable mounting rails supports installation in racks with front-to-rear rail distances between 28 inches (710 millimeters) minimum and 46 inches (1170 millimeters) maximum.

### Features

- Standard sliding shelf for installation in rack cabinets
- 28.3 in. / 72cm depth (29.5 in. / 74.9cm including handle)
- Supports up to 50 lbs (22.7 kgs)
- Extendable shelf can accommodate tower units, monitors and other equipment
- Designed for 4 post rack mounting and the required mounting hardware is included
- Expandable mounting rails supports installation in racks with front to rear rail distances between 28 in. / 71cm minimum and 46 in. / 117cm maximum

## Specifications

OVERVIEW	
UPC Code	037332144171
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	116.33



Powering Business Worldwide

TRIPP LITE  
SERIES

Maximum Device Depth (in.)	45.8
Maximum Device Depth (mm)	1,163
Minimum Device Depth (cm)	71.88
Minimum Device Depth (in.)	28.3
Minimum Device Depth (mm)	719
Shipping Dimensions (hwd / in.)	3.00 x 19.70 x 31.00
Shipping Dimensions (hwd / cm)	7.62 x 50.04 x 78.74
Shipping Weight (lbs.)	20.70
Shipping Weight (kg)	9.39
Unit Dimensions (hwd / in.)	1.750 x 19.000 x 29.500
Unit Dimensions (hwd / cm)	4.45 x 48.21 x 76.48
Unit Weight (lbs.)	18.6
Unit Weight (kg)	8.44
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.