

1421771

https://www.phoenixcontact.com/us/products/1421771

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, free cable end, on Valve connector CI (9.4 mm), Wiring: Z diode, cable length: 3 m

Commercial data

Item number	1421771
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF07
Product key	AF1DFA
GTIN	4055626279206
Weight per piece (including packing)	129.5 g
Weight per piece (excluding packing)	129.5 g
Customs tariff number	85444290
Country of origin	PL



1421771

https://www.phoenixcontact.com/us/products/1421771

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	3
No. of cable outlets	1
Shielded	no
Insulation characteristics	
Overvoltage category	III
Degree of pollution	3

Connection data

Conductor connection

Tightening torque	0.6 Nm
-------------------	--------

Material specifications

Flammability rating according to UL 94	V0
Seal material	TPU
Material housing valve plug	TPU
Contact material	CuSn
Valve plug contact insert material	PA 6.6
Contact surface material	Sn

Electrical properties

Nominal voltage U_N	110 V AC
	110 V DC
Nominal current I _N	4 A

Signaling

Status display	1 LED
Status display present	yes

Connector

Connection 1

Protective circuit

Туре	free cable end	
Connection 2		
Туре	Valve connector CI (9.4 mm)	
Material	CuSn (Contact)	
	Sn (Contact surface)	
	PA 6.6 (Contact carriers)	
	TPU (Housing)	

Z diode



1421771

https://www.phoenixcontact.com/us/products/1421771

С

Cable length	3 m
√C black [PVC]	
Dimensional drawing	
Cable weight	38.6 kg/km
UL AWM Style	2464
Number of positions	3
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	16x 0.20 mm
AWG signal line	20
Conductor cross section	3x 0.5 mm²
Wire diameter incl. insulation	1.5 mm ±0.05 mm
External cable diameter	4.80 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	39 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km
Nominal voltage, cable	300 V
Test voltage	1200 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	24 mm
Flame resistance	DIN VDE 0482
	DIN EN 50265-2-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C 80 °C (cable, fixed installation)
	-5 °C 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions



1421771

https://www.phoenixcontact.com/us/products/1421771

IP67




1421771

https://www.phoenixcontact.com/us/products/1421771


Drawings

Dimensional drawing



Valve connector, type CI

Dimensional drawing




Valve connector, type CI, side view




1421771

https://www.phoenixcontact.com/us/products/1421771

Schematic diagram



Valve connector connector pin assignment, type CI



Contact assignment of the valve plug



1421771

https://www.phoenixcontact.com/us/products/1421771

Classifications

ECLASS

ECLASS-13.0 27060312



1421771

https://www.phoenixcontact.com/us/products/1421771

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements Exemption	Yes 7(a)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com