

DE1E3KX102MN4AN01F

NRND

General

RoHS


REACH

125
°C max.

Safety
standard

Flow OK

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
A	Ammo Pack	500

Mass (typ.)	
1 piece	0.39g

Notices

X1/Y1 Class Certified Products, Halogen-free Products

Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE1E3KX102MN4AN01F



Specifications

L size or Outer diameter D	7.0mm max.
T size	7.0mm max.
Lead spacing F	10.0±1.0mm
Lead diameter d	0.6±0.05mm
Paint dripping e	Up to the end of crimp
Capacitance	1000pF ±20%
Rated voltage	250Vac(r.m.s.)
Temperature characteristics	E(JIS)
Capacitance change rate	+20/-55%
Temperature range of temperature characteristics	-25°C to 85°C
Operating Temperature Range	-40°C to 125°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE1E3KX102MN4AN01F




Characteristic Data


The charts below may show another part number which shares its characteristics.




■ DE1E3KX102MN4AN01F |Z| DC0V, 20degC



■ DE1E3KX102MN4AN01F R DC0V, 20degC



■ DE1E3KX102MN4AN01F C-DC bias capchange, 20.0degC, AC1



■ DE1E3KX102MN4AN01F C-AC Voltage capchange, DC0V, 20.0



Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE1E3KX102MN4AN01F



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.