

1-2199298-1 ✓ ACTIVE

## DIPLOMATE

TE Internal #: 1-2199298-1

Stamped & Formed, 6 Position, Low Profile, Through Hole, Tin (Sn),  
-40 – 105 °C [-40 – 221 °F], DIP Sockets

[View on TE.com >](#)



Connectors > Socket Connectors > IC Sockets > DIP Sockets



Contact Fabrication: **Stamped & Formed**

Number of Positions: **6**

Connector Profile: **Low**

Row-to-Row Spacing: **7.62 mm [ .3 in ]**

Leg Style: **Through Hole**

### Features

#### Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Leg Style	Through Hole

#### Configuration Features

PCB Mount Orientation	Vertical
Number of Rows	2
Number of Positions	6

#### Electrical Characteristics

Contact Resistance	20 mΩ
Insulation Resistance	1000 MΩ

#### Body Features

Sleeve Plating Material	Tin/Lead
Frame Style	Closed, Ladder
Sleeve Material	Brass/Copper
Connector Profile	Low

#### Contact Features

Mating Contact Type	Dual Leaf
Contact Base Material	Phosphor Bronze
IC Socket Type	DIP

PCB Contact Termination Area Plating Material	Tin
Contact Type	Pin
Contact Fabrication	Stamped & Formed
Contact Mating Area Plating Material	Tin (Sn)
Contact Mating Area Plating Material Thickness	1.52 µm[60 µin]
Contact Current Rating (Max)	1 A

### Termination Features

	3 in
Termination Method to PCB	Through Hole - Solder

### Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment Type	Polarization
Mating Alignment	With

### Housing Features

Housing Material	PBT GF30
Housing Color	Black
Centerline (Pitch)	2.54 mm[.1 in]

### Dimensions

Product Length	7.62 mm[.3 in]
Profile Height from PCB	5.1 mm[.2 in]
Row-to-Row Spacing	7.62 mm[.3 in]

### Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Tubes per Box	2
Packaging Method	Box & Tube, Tube
Packaging Quantity	80



Other

Quantity per Tube	8000
-------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

 <p>TE Part #1-745491-7 09 HDE MS RCPT,22-26,LEAD FREE</p>	 <p>TE Part #1-745492-8 09 HDE MS PLUG,22-26,LEAD FREE</p>	 <p>TE Part #3-794618-6 06P MICRO MNL ASSY R/A HDR LF</p>	 <p>TE Part #4-1437664-1 NC6-P108-08=NC6 ASSEMBLY</p>
---	---	--	--



TE Part #1623927-1  
CFR16 5% 100K




TE Part #3-2176344-1  
CRGCQ 1206 100K 5%



TE Part #5745394-2  
HD-20 RCPT 9P RA 318 THD INS



TE Part #2-5747704-0  
25 PLUG SP/FMS BRDLK



TE Part #1-350779-1  
04P UMNL V0 PLUG HSG BROWN



TE Part #103957-5  
4X6 MTE RCPT SR LATCH .100CL

## Documents

### Product Drawings

6P,DIP SKT,300 CL,LDR,PB FREE

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2199298-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2199298-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2199298-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[DIP Sockets Quick Reference Guide \(EN\)](#)

English