

**COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology with integrated high-pass filter**  
3407.17.0068

**Properties**

- Residual voltage reduced by 80 % compared to standard types of series 3400
- Residual energy reduced of more than 99.9 % compared to series 3401 and 3402
- DC-blocking on protected side of the device
- Available for applications from 70 MHz to 18 GHz
- Return loss 20 dB min. and Insertion loss 0.2 dB max.



Product configuration	
Main path connectors	Port 1: unprotected, N plug (male)
	Port 2: protected, N jack (female)
Mounting and grounding	MH110 (bulkhead mounting), M6 (screw)
Side of bulkhead	both
Inline design	YES
EMP can be install reversed	YES

Interface and material data	
Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Copper Beryllium / Bronze / Brass / Gold Plating (without Nickel underplating)
	Port 2: Brass / Gold Plating (without Nickel underplating)

Electrical data	
Impedance	50 Ω
Frequency frame	806 MHz to 2500 MHz
Return loss typical	26 dB
Insertion loss typical	0.1 dB
CW power frame	500 W
Residual pulse energy (typ.)	0.03 μJ (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Surge current handling capability	25 kA single, 20 kA multiple (test pulse 8/20 μs)

## COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology with integrated high-pass filter

3407.17.0068

Electrical remarks	
Gas tube	No DC / shorted QW or LC

Mechanical data	
Weight	538 g
Mating cycles	500

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP65, according to IEC 60529
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. A
Moisture resistance according	MIL-STD-202, Method 106

Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84002461	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table	
Item number	Item description
84002461	3407.17.0068

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P1960 / Date of publication: 28.02.2025 / uncontrolled copy