THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| — | — |


REVISIONS


| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | E | REVISED PER ECR-14-016288 | 20NOV2014 | NK | GJ |

1 PRODUCT SPECIFICATION: 108-5087.

2 APPLICATION SPEC: 114-5014.

3 PC BOARD THICKNESS 1.60±0.14[.063±.005]
HOLE DIAMETER $1.20^{+0.00}_{-0.03}[.047^{+.000}_{-.001}]$
(DRILL SIZE).




THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.40[.015]
3 PLC ± –
4 PLC ± –
ANGLES ± 1°

WIRE RANGE
0.05~0.15 mm² [.000071~.00023 SQ IN] (AWG #30-#26)

INSULATION DIA
0.66~1.22 mm [.026~.048 IN]

MATERIAL: BRASS

FINISH: POST PLATED TIN OVER Ni

| | | |
|---|---|---|
| DWN | H Skrobacki | 08/01/74 |
| CHK | G Sekel | 08/01/74 |
| APVD | S Tokarchuk | – |
| PRODUCT SPEC | — | |
| APPLICATION SPEC | — | |
| WEIGHT | — | |

TE Connectivity

NAME: MINI AMP-IN

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A3 | 00779 | C-170198 | — |

CUSTOMER DRAWING | SCALE 12:0 | SHEET 1 OF 1 | REV E



Downloaded from Arrow.com.