

Part Number : [1300360008](#)

Product Description : Mini-Change DeviceNet

Passive 6 Junction

Series Number : 130036

Status : Active

Product Category : Passive Distribution Boxes

Engineering Part Number : DN6000




Documents and Resources

Drawings

[1300360008_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Arsenic acid (H3AsO4), triethyl ester; Dibutylphthalate; Diarsenic-pentaoxide; Diarsenic-trioxide; 2,4-Dinitrotoluene; Tris(2-chloroethyl) phosphate; Tetraboron disodium heptaoxide, hydrate... per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	130036
Description	Mini-Change DeviceNet Passive 6 Junction
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	DeviceNet,Mini-Change
UPC	78678829996

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	7.0A
Functional Wiring	Parallel
Voltage - Maximum	120V AC/DC
Wiring Configuration	Passive Drop

Physical

Bus I/O	Mini-Change
Cable Connector Orientation	N/A
Cable Length	N/A

Home Run Cable Length	N/A
Home Run Connector	N/A
Home Run Interface	N/A
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	658.000/g
Orientation	Side Mount
Poles	5
Poles (wired)	5
Ports	6
Temperature Range - Operating	0° to +60°C

This document was generated on Apr 20, 2026