

HONEYWELL PART NUMBER
311SX54-H58
PRODUCT CODE VDS0410

REV	DOCUMENT	CHANGED BY	CHECK
5	0038558	SS 08MAY08	BLR



B

A

A

B

A



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA OF .188±.002 CENTERS
 - 2 PLATED TERMINALS WILL ACCEPT "AMP INC" .058 DIA PIN RECEPTACLES
 - 3 SWITCH WILL WITHSTAND TEMPERATURE OF 250° F
 - 4 CHARACTERISTICS ARE TAKEN AT POINT "A"

RELEASE NO. PR-16660

REPLACES

CHARACTERISTICS 4

OPERATING FORCE — — — 60 GRAM MAX

RELEASE FORCE — — — 11 GRAM MIN

DIFFERENTIAL TRAVEL — — .015 MAX

OVERTRAVEL — — — — .010 MIN

ELECTRICAL DATA				
CONTACT ARRANGEMENT S P D T				
	28 VOLTS DC RATING		115 VOLTS AC, 60 CPS	
	SEA LEVEL	50,000 FT	SEA LEVEL	
INDUCTIVE	3 AMP	2 AMP	5 AMP	
RESISTIVE	5 AMP	4 AMP	5 AMP	
-				
APPROVALS	KEMA, CE	5A 250 V ~ T125	5E4	 
	UL, CSA	5A <u>250</u> VAC	 	BRAND L4L

DESIGN UNITS: INCH		
TOLERANCES UNLESS NOTED:		
NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±
THIRD ANGLE PROJECTION		

DRAWN	SPK	26FEB08
CHECK	RJ	26FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell				
TITLE SWITCH - BASIC				
SIZE	TYPE	DRAWING NAME		REV
B	I	311SX54-H58		5
SCALE	-	WEIGHT: .003 LB MAX	SHEET 1 OF 1	