

## Contact insert module - HC-M-03-CT-F - 1414359

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Contact insert module, Number of positions: 3, Socket, Crimp connection, 690 V, 40 A, 1.5 mm² ... 10 mm², Application: Power

RoHS

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	5 STK
GTIN	 4 055626 025025
GTIN	4055626025025
Weight per Piece (excluding packing)	12.000 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Height	44.7 mm
Width	34.2 mm
Length	14.6 mm

#### Electrical characteristics

Note	For HEAVYCON housing type B6 to B48, HC-M-B...MF-... hinged module carrier frame required, CK4,0..... crimp contacts, crimp contacts not supplied as standard.
Rated voltage (III/3)	690 V
Rated current	40 A
Rated surge voltage	6 kV

# Contact insert module - HC-M-03-CT-F - 1414359

## Technical data

### Electrical characteristics

Connection profile	3
--------------------	---

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

### Mechanical characteristics

Conductor cross section	1.5 mm² ... 10 mm²
Connection cross section AWG	16 ... 8
Stripping length of the individual wire	9 mm (for 1.5 - 2.5 mm²)
	9.6 mm (for 4 mm² ... 6 mm²)
	15 mm (for 10 mm²/conductor ≥ 5 mm diameter)
	18 mm (for 10 mm²/conductor ≥ 6.4 mm diameter)
Wire diameter including insulation	7.5 mm
Insertion/withdrawal cycles	≥ 500
Minimum housing height	52 mm

### General

Series	HC-M-03
Color	light gray
Number of module slots	1
Connection method	Crimp connection
Connection in acc. with standard	IEC / EN
Flammability rating according to UL 94	V0
Degree of pollution	3
Overvoltage category	III
Assembly instructions	Housing height ≥ 52 mm. Plug-in connections may only be operated only when there is no load/voltage.
Connection	The CK4,0-EWZ tool (order no. 1662735) is required for removing the crimp contacts. At every "C" contact chamber, the position of the contact retaining springs is marked with two black markings on the connection side. From the connection side, the tool is pushed over the contact in a position-oriented manner, so that it touches both the retaining springs. Then insert it up to the limit stop. Do not turn the inserted tool. Push the conductor out of the insulating body along with the tool from the connection side.

### Material data

Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

### Standards and Regulations

Contact insert module - HC-M-03-CT-F - 1414359


Technical data

Standards and Regulations


Connection in acc. with standard	IEC / EN
Flammability rating according to UL 94	V0

Drawings

Schematic diagram




Diagram



Connector pin assignment

Derating diagram (6 modules in HC-B 24 housing)

Dimensional drawing



Approvals

Approvals

Approvals


EAC / UL Recognized / CSA


Ex Approvals


Approval details

## Contact insert module - HC-M-03-CT-F - 1414359

### Approvals

EAC		7500651.22.01.00246
-----	---	---------------------

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E118976
mm²/AWG/kcmil		10	
Nominal current I <sub>N</sub>		42 A	
Nominal voltage U <sub>N</sub>		600 V	

CSA		<a href="http://www.csagroup.org/services/testing-and-certification/certified-product-listing/">http://www.csagroup.org/services/testing-and-certification/certified-product-listing/</a>	13631
mm²/AWG/kcmil		10	
Nominal current I <sub>N</sub>		33 A	
Nominal voltage U <sub>N</sub>		600 V	