


RIGHT ANGLE MALE-MALE MMS**CABLE 2/50 S-BR, LENGTH: 60 CM****R284F0209003**Series : **CORD-SPECIF**

- * 1 * Connector A : **R209.353.000**
 * 2 * Connector B : **R209.353.000**
 * 3 * Cable : **C291.145.007**
 Type : **CAB HF 2/50 RG 178 BROWN**

ELECTRICAL CHARACTERISTICS

Impedance	50 Ω
Frequency	0-3 GHz
Operating temperature	-40/+90 ° C
VSWR	1.45 + 0.000 x F(GHz) Maxi
Insertion loss	1.15 $\sqrt{F}$(GHz) dB Maxi
Voltage rating	50 Veff Maxi
Dielectric withstanding voltage	250 Veff mini
Insulation resistance	500 MΩ mini

SPECIFICATION

Weight	4.950 g
Cable retention	20 N mini
Others :	



Edition : 0527 B

Design changes may be in order to improve the product.