
Part Number : 1700711012
Product Description : zSFP+ Stacked Ganged Assembly with Elastomeric Gasket, 2-by-1 with Inner Light Pipes, 40 Circuits
Series Number : 170071
Status : Active
Product Category : High-Speed I/O Connectors



Documents and Resources

Drawings

1700711012_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

SYM-170071-0001-001.zip

EE-170071-0001-001.pdf

SP-170426-1000-001.zip

Specifications

AS-170071-0002-001.pdf

PS-170071-0001-001.pdf

TS-170071-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Connectors
Series	170071
Description	zSFP+ Stacked Ganged Assembly with Elastomeric Gasket, 2-by-1 with Inner Light Pipes, 40 Circuits
Application	Module-to-Board
Component Type	Receptacle
Product Name	zSFP Plus,zSFP+
Type	Pluggable
UPC	884982401914

Agency

UL	E29179

Electrical

Current - Maximum per Contact	0.5A
Data Rate	28.0 Gbps
Shielded	Yes
Shield Type	N/A

Downloaded from Arrow.com.

Voltage - Maximum	30V AC

Physical

Circuits (Loaded)	40
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	27.808/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Downloaded from Arrow.com.

Global

Description	Part Number
Extraction Tool, 2 x 1 Medium	622029930

This document was generated on Aug 14, 2026

Downloaded from Arrow.com.