



- Plenum Suitable
- FAR 25 Approved
- Expands Up To 150%
- Resists Gasoline And Other Chemicals
- Cut And Abrasion Resistant

Put-Ups

Nominal Size	Part #	Expansion Range		Bulk Spool	Shop Spool	Available Colors	Lbs/ 100'
		Min	Max				
1/8"	TFN0.13NT	3/32"	1/4"	1,000'	225'	NT & BK	0.50
1/4"	TFN0.25NT	3/16"	3/8"	1,000'	200'	NT & BK	0.68
3/8"	TFN0.38NT	1/4"	3/4"	500'	125'	NT & BK	2.20
1/2"	TFN0.50NT	3/8"	7/8"	500'	100'	NT & BK	2.60
3/4"	TFN0.75NT	5/8"	1 1/4"	250'	75'	NT & BK	2.90
1 1/4"	TFN1.25NT	1 1/8"	1 1/2"	200'	50'	NT & BK	4.80
1 3/4"	TFN1.75NT	1 3/8"	1 3/4"	200'	50'	NT & BK	5.50
2"	TFN2.00NT	1 11/16"	2 1/8"	200'	25'	NT & BK	6.40



Cut Cleanly
Hot Knife

Material

Perfluoroalkoxy

Grade

TFN

Monofilament Diameter

.016"

Drawing Number

TF001TF-WD

High Temp Stable, Abrasion Resistant, Low Outgassing

TECHON PFA (TF) expandable sleeving is ideal in applications where flame, chemical and very high temperature resistance are significant considerations. Braided from 16 mil perfluoroalkoxy (PFA) polymer monofilament.

The high temperature properties of TF make it the ideal choice for aerospace, military and high-tech applications where thermal stability and low outgassing are critical. TF is suitable for plenum applications.


What Makes Techon PFA So Special?

Techon PFA is inert to virtually all chemicals and is considered the most slippery material on the planet. These properties have made it one of the most valuable and versatile technologies ever invented, contributing to advancements in areas such as aerospace, communications, electronics, industrial processes and architecture.

High temperature resistance and low outgassing allows Techon PFA sleeving to function in high-temp environments.

Colors Available:

Natural (NT) & Black(BK)



www.techflex.com

800.323.5140 • 973.300.9242 • fax: 973.300.9409
104 Demarest Road • Sparta, NJ 07871



FAR-25





ABRASION **FLAMMABILITY**

Abrasion Resistance
Very High

Rating _____ FAR 25

Abrasion Test Machine
Taber 5150

Abrasion Test Wheel
Calibrase H-18

Abrasion Test Load
500g

Room Temperature
71°F

Humidity
59%

Slight Rough Surface And
A Few Filaments Broken
1,500 Test Cycles

Visible Wear And Three
Filaments Broken
2,000 Test Cycles

Material Destroyed
3,000 Test Cycles

Pre-Test Weight
13,955.5 mg

Post-Test Weight
12,911.9 mg

Test End Loss Of Mass
Point Of Destruction
1,043.6 mg

CHEMICAL **RESISTANCE**

1=No Effect 4=More Affected
2=Little Effect 5=Severely Affected
3=Affected

Aromatic Solvents _____	1
Aliphatic Solvents _____	1
Chlorinated Solvents _____	1
Weak Bases _____	1
Salts _____	1
Strong Bases _____	1
Salt Water 0-S-1926 _____	1
Hydraulic Fluid MIL-H-5606 _____	1
Lube Oil MIL-L-7808 _____	1
De-Icing Fluid MIL-A-8243 _____	1
Strong Acids _____	1
Strong Oxidants _____	1
Esters/Ketones _____	2
UV Light _____	1
Petroleum _____	1
Fungus ASTM G-21 _____	1
Halogen Free _____	No
RoHS _____	Yes
SVHC _____	

Melt Point
ASTM D-2117
590°F (310°C)

Maximum Continuous
Mil-I-23053
550°F (280°C)

Minimum Continuous
-94°F (-70°C)



PHYSICAL **PROPERTIES**

Monofilament Diameter _____ .016
ASTM D-204

Flammability Rating _____ FAR 25

Recommended Cutting _____ Hot Knife

Colors _____ 2

Wall Thickness _____ .04

Tensile Strength (Yarn) _____ 2.1
ASTM D-2256 Lbs

Specific Gravity ASTM D-792 _____ 2.15

Moisture Absorption _____ <.01
% ASTM D-570

Hard Vacuum Data _____
ASTM E-595 at 10-5 torr

TML _____ .00

CVCM _____ .00

WVR _____ 0

Smoke D-Max _____
ASTM E-662

Outgassing _____ Very Low

Oxygen Index _____ >95
ASTM D-2863

© 2016 Techflex, Inc. - Any unauthorized reproduction, in whole or part, in any medium whatsoever, without the express written permission of Techflex, Inc. is strictly forbidden.

Techflex product names and logos are registered trademarks of Techflex, Inc., unless otherwise attributed. The contents and illustrations contained herein are believed to be reliable. Techflex makes no warranties as to their accuracy or completeness and disclaims any liability in connection with their use. Techflex's only obligations are those in standard terms of sale for these products and Techflex will not be liable for any consequential or other damages arising due to misuse of these products or typographical errors or omissions. Users should make their own evaluation to determine the suitability of these products for their unique and specific applications.