






- NOTE:
1. ELECTRICAL CHARACTERISTICS
 - 1-1 RATING CURRENT: 3A AC/DC
 - 1-2 RATING VOLTAGE: 250V AC/DC
 - 1-3 WITHSTANDING VOLTAGE: 800V AC/1MINUTE
 - 1-4 OPERATING TEMPERATURE: -40°C~+105°C
 - 1-5 INSULATION RESISTANCE: 1000M ohm MIN
 2. MATERIAL: REFER TO ORDERING CODE
 3. FINISH: BRIGHT TIN PLATING
 4. INSULATION O.D.: Ø1.70MM MAX
- WIRE SIZE: AWG#22~26 (0.35~0.13mm²)
5. USED WITH AFCI 10156616
 6. PRODUCT SPEC: GS-12-1595
 7. ORDERING CODE: 10156617-X 0 0 X LF

MATERIAL _____ PACKAGE
4: BRASS
1: REEL
2: PHOSPHOR BRONZE



mat'l. code				surface		tolerance	projection	product family	
ltr	ecn no	dr	date	ISO 1302	ISO 406	ISO	1104	MINITEK	
A	New release	Jason	2020-2-19	tolerances unless otherwise specified				title	
B	ELX-N-36610	Jason	2020-4-2	angles	linear	.X±.3 .XX±.20	mm	2.5PITCH BOARD-IN, R/A , TERMINAL	
				0°±x'	.XXX±.10	scale 2:1		dwg no	sheet 1 of 1
		dr	Jason Wang	2020-1-19				10156617	size A3
		engr	Jason Wang	2020-4-2					
		chr	-						
		qppd	Tim Yao	2020-4-2				type	Product Customer Drawing
sheet index	revision	sheet	1						