


SHEET 1 OF 1




PCB MOUNTING




PANAL CUTOUT







▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
ON	NONE	ON
2-3	N/A	2-1



CIRCUIT: SPDT





NOTE:
1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
   X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
▲ 4. PLATING MATERIAL: SILVER
5. RATING: 3 AMPS @ 120VAC or 28VDC UL, CUL
   1 AMPS @ 250VAC UL, CUL
6. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
   AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
9. OPERATING TEMP.: -40°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. HARDWARE INCLUDED: T200001 - HEXNUT (2)
    T200000 - LOCKWASHER (1)
    T200002 - LOCKRING (1)

REV	ECO NO	DESCRIPTION	DATE	BY
D	ECO-103186	print update	01/24/25	MW

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E•SWITCH®

OBJECT ID 000023273

TITLE 200MSP1T1B1M2QEH

SCALE	DATE	DR	DWG	REV
2:1	3/6/2007	MM	ST211018	D

Downloaded from Arrow.com.