

MODS-D, MODS-E SERIES

SINGLE VERTICAL & SMT MODULAR JACKS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MODS-D

Insulator Material:

Nylon 46/ PBT Glass Filled

(Nylon for -SM, PBT for -TH)

Contact Material:

Phosphor Bronze

Shield Material:

Copper Alloy

Plating:

Gold on Contacts,

Nickel on Shield, Tin on Tails

Operating Temp Range:

-25°C to +90°C

Current Rating:

1.5 A per contact

Voltage Rating:

120 VAC

Contact Resistance:

20 mΩ max

Minimum Cycles:

500

System Applications:

CAT3

Packaging:

Packaged and shipped in

Bulk Packaging Trays; Trays

suitable for automation are

available upon request.

RoHS Compliant:

Yes

Lead-Free Solderable:

-SM=Yes

-TH=Yes (Wave Solder only)



MODS

D

POSITIONS
CONTACTS

PLATING

SHIELD
OPTION

TAIL

-6P4C = 6 Positions 4 Contacts

-6P6C = 6 Positions 6 Contacts

-8P8C = 8 Positions 8 Contacts

-L
= 15μ" (0,38 μm) Gold on
Mating Area, Gold Flash on Tails

-U
= 50μ" (1,27 μm) Gold on
Mating Area, Gold Flash on Tails


(Leave Blank for
Unshielded)

-S
= Shielded

-N
= No Panel Stops
(Unshielded Only)

-SM
= Surface
Mount

-TH
= Through-
hole



POSITIONS CONTACTS	A	B	B (-S)
-6PXC	(15,90) .626	(13,30) .524	(14,10) .555
-8P8C	(17,80) .701	(15,20) .598	(16,00) .630

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MODS-E

Insulator Material:

PBT Glass Filled

Contact Material:

Phosphor Bronze

Shield Material:

Copper Alloy

Plating:

Gold on Contacts,

Nickel on Shield

Operating Temp Range:

-25°C to +90°C

Current Rating:

1.5 A per contact

Voltage Rating:

120 VAC

Contact Resistance:

20 mΩ max

Minimum Cycles:

500

System Applications:

CAT3

Packaging:

Packaged and shipped in

Bulk Packaging Trays; Trays

suitable for automation are

available upon request.

RoHS Compliant:

Yes

Lead-Free Solderable:

Yes (Wave Solder only)



MODS

E

POSITIONS
CONTACTS

PLATING

SHIELD
OPTION

-4P4C = 4 Positions 4 Contacts

-6P4C = 6 Positions 4 Contacts

-6P6C = 6 Positions 6 Contacts

-8P8C = 8 Positions 8 Contacts

Unshielded Only

-G
= 15μ" (0,38 μm)
Gold on Mating Area,
Gold Flash on Tails

-E
= 50μ" (1,27 μm)
Gold on Mating Area,
Gold Flash on Tails

Shielded Only


-L
= 15μ" (0,38 μm)
Gold on Mating Area,
Gold Flash on Tails

-U
= 50μ" (1,27 μm)
Gold on Mating Area,
Gold Flash on Tails

(Leave Blank for
Unshielded)

-S
= Shielded
(-4P4C and Panel
Stops N/A)

POSITIONS CONTACTS	A	B
-4P4C	(13,80) .543	(11,43) .450
-6PXC	(15,90) .626	(13,46) .530
-8P8C	(17,90) .705	(15,50) .610



APPLICATION SPECIFIC OPTION

- No panel stop option available
- Other plating options available
- Call Samtec.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 8890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292 SAMTEC ISRAEL • Tel: 972-3-7526600
 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766 SAMTEC TAIWAN • Tel: 886-2-2735-6109
 6904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9512 7747 SAMTEC SOUTH AFRICA • Tel: 27 11 452 8112