



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	PRODUCTION ISSUE	31JAN2019	PNT	MT

a) Part as supplied



b) Part after unrestricted recovery



DIMENSIONS in millimetres[inches]

	H		J		P		R	S	T	HW	JW
Part No.	min	max	min	max	±10%	±10%	±10%	±10%	±10%	±20%	±20%
	a	b	a	b	b	b	b	b	b	b	b
243D012-12-G04	20 [.79]	14.2 [.56]	20 [.79]	4.1 [.16]	24 [.94]	10 [.39]	3.0 [.12]	1.1 [.04]	2.3 [.09]	1.8 [.07]	
243D022-12-G04	24 [.94]	17.8 [.70]	24 [.94]	5.6 [.22]	27 [1.06]	10 [.39]	3.0 [.12]	1.1 [.04]	2.8 [.11]	1.9 [.07]	
#			#								

THIS IS AN OVEREXPANDED VARIANT MODIFIED DIMENSIONS ARE SHOWN THUS: - #

DIMENSIONS: mm [INCHES]	DWN	31JAN2019	MATERIAL	SEE SHEET 2	FINISH	-
	CHK	31JAN2019	 TE Connectivity Ltd.			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	31JAN2019				
0 PLC ± -	PRODUCT SPEC	-				
1 PLC ± -	APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ± -			A4	00779	C-243D0XX-12-G04-0	-
3 PLC ± -	WEIGHT		CUSTOMER DRAWING			
4 PLC ± -			SCALE	DNS	SHEET	1 OF 2
ANGLES ± -					REV	2

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-12	Fluoroelastomer, flexible	RT-1312	N/A	N/A

Ordering Information

243D0XX-XX-GXX-0




RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T	31JAN2019	MATERIAL —	FINISH —		
	CHK N NAGAR	31JAN2019	 TE Connectivity Ltd.			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD M TAYLOR	31JAN2019				
	PRODUCT SPEC —	NAME BOOT, 135 DEG				
	APPLICATION SPEC —	—				
	WEIGHT	—	SIZE A4	CAGE CODE 00779	DRAWING NO C-243D0XX-12-G04-0	RESTRICTED TO —
	CUSTOMER DRAWING			SCALE DNS	SHEET 2 of 2	REV 2