








REV.	DATE	ECR NO.	DESCRIPTION
NC	11/21/06	—	INITIAL RELEASE
A	09/02/08	—	REVISE BARREL O.D./ REVISE FERRULE I.D. AND O.D.



RECOMMENDED
CABLE STRIPPING DIM'S



RECOMMENDED
MOUNTING HOLE



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .128" [3.25]
2. CONTACT PIN TO SOLDER

						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex										
8	HEAT SHRINK TUBING				1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm		DRAWN		GRS						09/02/08						
7	FERRULE	COPPER	GOLD	1			UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”		CHECKED													
6	HEX NUT	BRASS	GOLD	1					ISSUED				PART DESCRIPTION									
5	LOCK WASHER	BRASS	GOLD	1					SHEET		1 OF 1		SMA REVERSE POLARITY BULKHEAD CRIMP PLUG (FOR RG-174/U, 188A/U, 316/U CABLE)									
4	GASKET	SILICONE	RED	1									PART NO.									
3	CONTACT PIN	BER. COPPER	GOLD	1									132284RP									
2	INSULATOR	PTFE	NATURAL	1					CAD FILE		C:/132/132284RP.DWG		DWG. NO.		132284RP.DWG	REV.	A	SIZE	A	SCALE	NA	
1	BODY	BRASS	GOLD	1																		
	DESCRIPTION	MATERIAL	FINISH	QTY			DO NOT SCALE DRAWING															