



## Product Navigation

[Home](#) [About Us](#) [Products](#) [Investor Relations](#) [News](#) [Contact Us](#) [Secure EAX](#)

### Circuit Board Indicators

### Panel Mount Indicators

### Solid State Lighting

### Traffic Signals

### Vehicle Lighting

### Rail

### Obstruction Lighting

### Hazardous Area Lighting

### Heliport Lighting

### how to purchase

[sales contacts](#)

[stock check](#)

### search

[Product Line Search](#)

Please select a Product Line to search.

[Circuit Board Indicators](#)

[find](#)

[Part # / Text Search](#)

[Part No.:](#)

[Text Search:](#)

[search](#)

### quick links

#### Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

#### Application Notes FAQs

[Dialight Ltd \(UK\)](#)  
[Dialight Garufo](#)  
[Dialight BLP](#)  
[LumiDrives](#)

P/N# **5530323F**

3 mm Lens

### Absolute Maximum Ratings (Ta = 25 ° )

Solder Temp **260° for 5 sec**  
Operating Temp **-40 to +85° C**  
Storage Temp **-55 to +100° C**

### Distributor Stock Check

Check stock with our distributors now.

5530323F

[check stock](#)



view PDF

### Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2
Color	Green	Yellow
Lamp Type	Single Color	Single Color
LED Type	Integral Resistor	Integral Resistor
Intensity Min (mcd)	5.6	3.7
Intensity Typ (mcd)	19.0	12.6
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)		
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		