30A BI-DIRECTIONAL SURFACE-MOUNT THYRISTOR SURGE PROTECTIVE DEVICE

Features


- 30A Peak Pulse Current @ 10/1000μs
- 150A Peak Pulse Current @ 8/20μs
- 58V - 320V Stand-Off Voltages
- Oxide-Glass Passivated Junction
- Bi-directional Protection in a Single Device
- High Off-State Impedance and Low On-State Voltage
- Helps Equipment Meet GR-1089-CORE, IEC 61000-4-5, FCC Part 68, ITU-T K.20/K.21, and UL 497B
- UL Recognized File # E219635
- **Lead-Free Finish; RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/**

Mechanical Data

- Package: SMB
- Package Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Plating (Matte Tin Finish). Solderable per MIL-STD-202, Method 208 e3
- Polarity: None; bi-directional devices have no polarity indicator.
- Weight: 0.093 grams (Approximate)



Top View




Bottom View

Ordering Information (Note 3)

Orderable Part Number	Package	Packing	
		Qty.	Carrier
TB0640L-13-F	SMB	3,000	Tape & Reel
TB0720L-13-F	SMB	3,000	Tape & Reel
TB0900L-13-F	SMB	3,000	Tape & Reel
TB1100L-13-F	SMB	3,000	Tape & Reel
TB1300L-13-F	SMB	3,000	Tape & Reel
TB1500L-13-F	SMB	3,000	Tape & Reel
TB1800L-13-F	SMB	3,000	Tape & Reel
TB2300L-13-F	SMB	3,000	Tape & Reel
TB2600L-13-F	SMB	3,000	Tape & Reel
TB3100L-13-F	SMB	3,000	Tape & Reel
TB3500L-13-F	SMB	3,000	Tape & Reel

Notes:
1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



xxxxx = Product Type Marking Code (See Table on Page 3)
= Manufacturer's Code Marking
YWW = Date Code Marking
Y = Last Digit of Year (ex: 6 for 2026)
WW = Week Code (01 to 53)
A Bar or Underline around the Date Code or Product Type Marking Code Denotes Assembly Site if Marked

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load.
For capacitance load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Non-Repetitive Peak Impulse Current @10/1000µs	I_{pp}	30	A
Non-Repetitive Peak On-State Current @8.3ms (One-Half Cycle)	I_{TSM}	15	A
Typical Positive Temperature Coefficient for Breakdown Voltage	$\Delta V_{BR}/\Delta T_J$	0.1	%/°C


Thermal Characteristics

Characteristic	Symbol	Value	Unit
Thermal Resistance, Junction to Lead	$R_{\theta JL}$	30	°C/W
Thermal Resistance, Junction to Ambient	$R_{\theta JA}$	120	°C/W
Junction Temperature Range	T_J	-40 to 150	°C
Storage Temperature Range	T_{STG}	-55 to 150	°C

Maximum Rated Surge Waveform

Current Waveform	Voltage Waveform	Standard	I_{pp} (A)
2/10µs	2/10µs	GR-1089-CORE	200
8/20µs	1.2/50µs	IEC 61000-4-5	150
10/160µs	10/160µs	FCC Part 68	100
5/310µs	10/700µs (Note 4)	ITU-T K.20/K.21	60
10/560µs	10/560µs	FCC Part 68	50
10/1000µs	10/1000µs	GR-1089-CORE	30

Note: 4. Applied 2kV, 10/700µs waveform.




© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Part Number	Maximum Off-State Leakage Current @ V_{DRM}		Maximum Breakover Voltage	Maximum On-State Voltage @ I_T = 1A	Breakover Current I_{BO}		Holding Current I_H		Typical Off-State Capacitance	Marking Code
	I_{DRM} (μA)	@ V_{DRM} (V)	V_{BO} (V)	V_T (V)	Min (mA)	Max (mA)	Min (mA)	Max (mA)	C_O (pF)	
TB0640L	5	58	77	3.5	50	800	150	800	100	T064L
TB0720L	5	65	88	3.5	50	800	150	800	100	T072L
TB0900L	5	75	98	3.5	50	800	150	800	100	T090L
TB1100L	5	90	130	3.5	50	800	150	800	60	T110L
TB1300L	5	120	160	3.5	50	800	150	800	60	T130L
TB1500L	5	140	180	3.5	50	800	150	800	60	T150L
TB1800L	5	160	220	3.5	50	800	150	800	60	T180L
TB2300L	5	190	265	3.5	50	800	150	800	40	T230L
TB2600L	5	220	300	3.5	50	800	150	800	40	T260L
TB3100L	5	275	350	3.5	50	800	150	800	40	T310L
TB3500L	5	320	400	3.5	50	800	150	800	40	T350L

Symbol	Parameter
V_{DRM}	Stand-Off Voltage
I_{DRM}	Leakage Current at Stand-Off Voltage
V_{BR}	Breakdown Voltage
I_{BR}	Breakdown Current
V_{BO}	Breakover Voltage
I_{BO}	Breakover Current
I_H	Holding Current (Note 5)
V_T	On-State Voltage
I_{PP}	Peak Pulse Current
C_O	Off-State Capacitance (Note 6)

Notes: 5. $I_H > (V_L/R_L)$; if this criterion is not obeyed, the TSPD triggers but does not return correctly to high-resistance state. The surge recovery time does not exceed 30ms.
6. Off-state capacitance measured at f = 1.0MHz, $1.0V_{RMS}$ signal, $V_R = 2V_{DC}$ bias.



© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.




Fig. 1 Off-State Current vs. Junction Temperature




Fig. 2 Relative Variation of Breakdown Voltage vs. Junction Temperature




Fig. 3 Relative Variation of Breakover Voltage vs. Junction Temperature




Fig. 4 On-State Current vs. On-State Voltage




Fig. 5 Relative Variation of Holding Current vs. Junction Temperature





Fig. 6 Relative Variation of Junction Capacitance vs. Reverse Voltage Bias

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SMB




SMB		
Dim	**Min**	**Max**
A	2.00	2.50
A1	0.05	0.20
b	1.96	2.21
c	0.15	0.31
D	3.30	3.94
E	5.00	5.59
E1	4.06	4.57
L	0.76	1.52
All Dimensions in mm		

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SMB



Dimensions	Value (in mm)
C	4.30
G	1.80
X	2.50
X1	6.80
Y	2.30

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2026 Diodes Incorporated. All Rights Reserved.

www.diodes.com

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.