




3M™ TWIN AXIAL PCI EXPRESS X16 MALE-TO-MALE CABLE ASSEMBLY



BILL OF MATERIALS			
	ITEM	DESCRIPTION	QTY
1.0	PCB	PCIE X16 EXTENDER (164 POS) CARD-EDGE INVERSE 3M P/N: 78-9101-8788-5	1
2.0	PCB	PCIE X16 EXTENDER (164 POS) CARD-EDGE 3M P/N: 78-9101-6804-2	1
3.0	CABLE	RIBBON TWIN AX CABLE 3M P/N: SL8802/22-18DN5-00	4
4.0	CABLE	RIBBON CABLE, 20 POSITION 3M P/N: 3749-20	2
5.0	STRAIN RELIEF	ADHESIVE	AS REQUIRED

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3mconnectors.com>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

- NOTES
- DIMENSIONS ARE IN MILLIMETERS.
 - 3M™ RIBBON TWINAX DESCRIPTION:
30 AWG, SILVER PLATED SIGNAL WIRE
IMPEDANCE: 85 ±5 OHM
OVERALL RIBBON WIDTH: 24.90 MM
OVERALL RIBBON THICKNESS: 0.75 MM
 - ROHS COMPLIANT. SEE REGULATORY
INFORMATION APPENDIX IN "ROHS
COMPLIANCE" SECTION AT
WWW.3MCONNECTORS.COM
(E1 & C1 APPLY)
 - THIS CABLE CONSTRUCTION
HAS A THIN ALUMINUM LAYER
AT EACH EDGE. USER SHOULD
EVALUATE ITS USE IN THEIR
APPLICATION AND, IF NECESSARY,
INSULATING TAPE MAY BE APPLIED TO
COVER THE ALUMINUM LAYER, AS USER
DEEMS APPROPRIATE.
 - APPLICABLE SPECIFICATIONS:
PRODUCT SPECIFICATION NUMBER:
TWIN AX CABLE: PS-0106
CABLE ASSEMBLY: PS-0137
 - ORDER BY APPLICABLE 3M PART NUMBER:
8KC5-0742-XXXX

XXXX = DIM 'A' IN MILLIMETERS
(1000 = 1 METER)

STANDARD LENGTH (DIM 'A')
8KC5-0742-0250 (250 MM)
8KC5-0742-0500 (500 MM)

NON-STANDARD LENGTHS AVAILABLE
UPON SPECIAL REQUEST. MAY REQUIRE
HIGHER MOQS AND LONGER LEAD TIMES.
 - FLAMMABILITY RATING:
TWIN AX CABLE: UL94 HB
PCBS: UL94V-0
 - PADDECARD FINGER GOLD THICKNESS:
0.76 µm [30 µ"] MIN ELECTROLYTIC
HARD GOLD OVER 1.27 µm [50 µ"]
MIN ELECTROLYTIC NICKEL.

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
ACCESS CODES				DRFT	L	SCHMIDT	DATE MAR 27, 2013	MFG	DATE
				CHKD			DATE	APPR T SUNIGA	DATE MAR 28, 2013
DIVISION		DIVISION CODE		© 3M COPYRIGHT 2017					
DO NOT SCALE DRAWING		SCALE 1 1		TOLERANCES EXCEPT AS NOTED		3M 3M Center St. Paul, MN 55144 This document and the information it contains are 3M property and may not be reproduced or further distributed without the permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
		INCHES .00 ± .000 ± 2000 ±		TITLE 8KC5-0742-XXXX, CABLE ASSY, MALE PCIE X16 TO MALE PCIE X16					
THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 2009		MILLIMETERS 0 ±.1 .00 ±.5 .000 ±.005		CAGE NUMBER D 78-5160-2586-5		REV. C	
MAX SURFACE ROUGHNESS 125 ✓		ALL SURFACES MARKED ONLY		ANGLES ±1°		MODEL		DET. LISTS <input type="checkbox"/> YES <input checked="" type="checkbox"/> NO SHT 1 OF 6	

3M 3749-20 Cable	
Wire #	Pin Attachment #
01	Ground Layer
02	B01 - B02
03	B01 - B02
04	B01 - B02
05	B01 - B02
06	B01 - B02
07	B01 - B02
08	Ground Layer
09	B05
10	B06
11	Ground Layer
12	B08
13	B08
14	B09
15	B10
16	B10
17	Ground Layer
18	B11
19	Ground Layer
20	B12

3M SL8802 Cable	
Wire #	Pin Attachment
GND	Ground Layer
pr_01	B14
pr_01	B15
pr_02	B17
pr_02	Ground Layer
pr_03	B19
pr_03	B20
pr_04	B23
pr_04	B24
GND	Ground Layer
pr_05	B27
pr_05	B28
pr_06	B30
pr_06	B31
pr_07	B33
pr_07	B34
GND	Ground Layer
pr_08	B37
pr_08	B38
pr_09	B41
pr_09	B42
pr_10	B45
pr_10	B46
pr_11	B48
pr_11	Ground Layer
GND	Ground Layer


3M SL8802 Cable	
Wire #	Pin Attachment #
GND	Ground Layer
pr_01	B50
pr_01	B51
pr_02	Ground Layer
pr_02	Ground Layer
pr_03	B54
pr_03	B55
pr_04	B58
pr_04	B59
GND	Ground Layer
pr_05	B62
pr_05	B63
pr_06	B66
pr_06	B67
pr_07	B70
pr_07	B71
GND	Ground Layer
pr_08	B74
pr_08	B75
pr_09	Ground Layer
pr_09	Ground Layer
pr_10	B78
pr_10	B79
pr_11	B81
pr_11	B82
GND	Ground Layer


PCI-Express X16 Pin-Out			
Pin #	Side B Description	Side A Description	Pin #
B01	+12 volt power	Hot plug presence detect	A01
B02	+12 volt power	+12 volt power	A02
B03	+12 volt power	+12 volt power	A03
B04	Ground	Ground	A04
B05	SMBus clock	TCK	A05
B06	SMBus data	TDI	A06
B07	Ground	TDO	A07
B08	+3.3 volt power	TMS	A08
B09	+TRST#	+3.3 volt power	A09
B10	3.3v volt power	+3.3 volt power	A10
B11	Link Reactivation	Power Good	A11
Mechanical Key			
B12	Reserved	Ground	A12
B13	Ground	Reference Clock	A13
B14	Transmitter Lane 0,	Differential pair	A14
B15	Differential pair	Ground	A15
B16	Ground	Receiver Lane 0,	A16
B17	Hotplug detect	Differential pair	A17
B18	Ground	Ground	A18
B19	Transmitter Lane 1,	Reserved	A19
B20	Differential pair	Ground	A20
B21	Ground	Receiver Lane 1,	A21
B22	Ground	Differential pair	A22
B23	Transmitter Lane 2,	Ground	A23
B24	Differential pair	Ground	A24
B25	Ground	Receiver Lane 2,	A25
B26	Ground	Differential pair	A26
B27	Transmitter Lane 3,	Ground	A27
B28	Differential pair	Ground	A28
B29	Ground	Receiver Lane 3,	A29
B30	Reserved	Differential pair	A30
B31	Hot plug detect	Ground	A31
B32	Ground	Reserved	A32
B33	Transmitter Lane 4,	Reserved	A33
B34	Differential pair	Ground	A34
B35	Ground	Receiver Lane 4,	A35
B36	Ground	Differential pair	A36
B37	Transmitter Lane 5,	Ground	A37
B38	Differential pair	Ground	A38
B39	Ground	Receiver Lane 5,	A39
B40	Ground	Differential pair	A40
B41	Transmitter Lane 6,	Ground	A41
B42	Differential pair	Ground	A42
B43	Ground	Receiver Lane 6,	A43
B44	Ground	Differential pair	A44
B45	Transmitter Lane 7,	Ground	A45
B46	Differential pair	Ground	A46
B47	Ground	Receiver Lane 7,	A47
B48	Hot plug detect	Differential pair	A48
B49	Ground	Ground	A49
B50	Transmitter Lane 8,	Reserved	A50
B51	Differential pair	Ground	A51
B52	Ground	Receiver Lane 8,	A52
B53	Ground	Differential pair	A53
B54	Transmitter Lane 9,	Ground	A54
B55	Differential pair	Ground	A55
B56	Ground	Receiver Lane 9,	A56
B57	Ground	Differential pair	A57
B58	Transmitter Lane 10,	Ground	A58
B59	Differential pair	Ground	A59
B60	Ground	Receiver Lane 10,	A60
B61	Ground	Differential pair	A61
B62	Transmitter Lane 11,	Ground	A62
B63	Differential pair	Ground	A63
B64	Ground	Receiver Lane 11,	A64
B65	Ground	Differential pair	A65
B66	Transmitter Lane 12,	Ground	A66
B67	Differential pair	Ground	A67
B68	Ground	Receiver Lane 12,	A68
B69	Ground	Differential pair	A69
B70	Transmitter Lane 13,	Ground	A70
B71	Differential pair	Ground	A71
B72	Ground	Receiver Lane 13,	A72
B73	Ground	Differential pair	A73
B74	Transmitter Lane 14,	Ground	A74
B75	Differential pair	Ground	A75
B76	Ground	Receiver Lane 14,	A76
B77	Ground	Differential pair	A77
B78	Transmitter Lane 15,	Ground	A78
B79	Differential pair	Ground	A79
B80	Ground	Receiver Lane 15,	A80
B81	Hot plug present detect	Differential pair	A81
B82	Hot Plug Detect	Ground	A82

3M 3749-20 Cable	
Pin Attachment #	Wire #
Ground Layer	01
A01	02
Ground Layer	03
A02 - A03	04
A02 - A03	05
A02 - A03	06
A02 - A03	07
Ground Layer	08
A05	09
A06	10
A07	11
A08	12
Ground Layer	13
A09 - A10	14
A09 - A10	15
A09 - A10	16
A09 - A10	17
Ground Layer	18
Ground Layer	19
A11	20

3M SL8802 Cable	
Pin Attachment #	Wire #
Ground Layer	GND
A13	pr_01
A14	pr_01
A16	pr_02
A17	pr_02
Ground Layer	pr_03
A19	pr_03
A21	pr_04
A22	pr_04
Ground Layer	GND
A25	pr_05
A26	pr_05
A29	pr_06
A30	pr_06
A32	pr_07
A33	pr_07
Ground Layer	GND
A35	pr_08
A36	pr_08
A39	pr_09
A40	pr_09
A43	pr_10
A44	pr_10
A47	pr_11
A48	pr_11
Ground Layer	GND

3M SL8802 Cable	
Pin Attachment #	Wire #
Ground Layer	GND
A50	pr_01
Ground Layer	pr_01
A52	pr_02
A53	pr_02
Ground Layer	pr_03
Ground Layer	pr_03
A56	pr_04
A57	pr_04
Ground Layer	GND
A60	pr_05
A61	pr_05
A64	pr_06
A65	pr_06
A68	pr_07
A69	pr_07
Ground Layer	GND
A72	pr_08
A73	pr_08
A76	pr_09
A77	pr_09
Ground Layer	pr_10
Ground Layer	pr_10
A80	pr_11
A81	pr_11
Ground Layer	GND

C	77002	DEC 14, 2017		AD	LS
		PIN DEFINITION A50 WAS A33, ZONE B4, SH2; ADDED SH3 WARRANTY INFO			
B	48418	JUN 19, 2013			LDS TS
		ADDED SIDE A & SIDE B INDICATORS			
A	46893	MAR 27, 2013			LDS TS
		WORK REQUEST 11618 INITIAL RELEASE			
REV	ECO	ISSUE DATE AND DESCRIPTION			DRFT
DRFT	L	DATE	MFG	DATE	
SCHMIDT		MAR 27, 2013			
CHKD		DATE	APPROV	DATE	
			T SUNIGA	MAR 28, 2013	
 <div> <div>3M Center</div> <div>St. Paul,</div> <div>MN 55144</div> </div>		<div>© 3M COMPANY 2017</div> <div>This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M's permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.</div>			
		TITLE			
8KC5-0742-XXXX, CABLE ASSY, MALE PCIE X16 TO MALE PCIE X16					
CAGE NUMBER	SIZE	DRAWING NO.			REV.
D		78-5100-2586-5			C
MODEL	DET.		LISTS		
		YES <input type="checkbox"/> NO <input checked="" type="checkbox"/>		SHT 2 OF 2	



THIS IS A FEED THROUGH ASSEMBLY. THE PIN ASSIGNMENTS REMAIN THE SAME ON BOTH ENDS.

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M Electronics Materials Solutions Division
6801 River Place Blvd.
Austin, TX 78726-9000
1-800-225-5373
www.3M.com/interconnect

C		4700		DEC 14, 2017		AD		LS	
				PIN DEFINITION A50 WAS A33, ZONE B4, SH2: ADDED SH3 WARRANTY INFO					
B		48418		JUN 19, 2013		LDS		TS	
				ADDED SIDE A & SIDE B INDICATORS					
A		46893		MAR 27, 2013		LDS		TS	
				WORK REQUEST 11618 INITIAL RELEASE					
REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
DRFT		L SCHMIDT		DATE MAR 27, 2013		APPROV T SUNIGA		DATE MAR 28, 2013	
CHKD				DATE					
DIVISION				DIVISION CODE					
DO NOT SCALE DRAWING		SCALE 1 1		TOLERANCES EXCEPT AS NOTED		INCHES 0 ± .00 ± .000 ± .0000		MILLIMETERS 0 ± .5 ± .005 ± .005	
THIRD ANGLE PROJECTION									
INTERPRET PER ASME Y14.5 - 2009									
MAX SURFACE ROUGHNESS 125		<input type="checkbox"/> ALL SURFACES <input checked="" type="checkbox"/> MARKED ONLY		ANGLES ± 1°					
3M		3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2017 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.					
TITLE				8KC5-0742-XXXX, CABLE ASSY, MALE PCIE X16 TO MALE PCIE X16					
CATEGORY		SIZE		DRAWING NO.		C		REV.	
NUMBER		D		78-5100-2586-5		C			
MODEL				DET. LISTS		YES <input type="checkbox"/> NO <input checked="" type="checkbox"/>		SHT 3 OF 3	