molex

Part Number : 2010215258
Product Description : Slim-Grid Header, 8 Circuits, Through Hole, Right-Angle, Shrouded, 0.76µm Gold (Au) Plated, 3.00mm Tail Length, with Peg, with Pick-and-Place Polyimide Tape, Tube, Lead-Free
Series Number : 201021
Status : Obsolete
Product Category : Board-to-Board Connectors

Obsolete

Documents and Resources

Drawings

2010215258_sd.pdf

2010215258_stp.zip

Symbol and Footprint (Multi-Format)

Specifications

2009890001-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Board-to-Board Connectors
Series	201021
Description	Slim-Grid Header, 8 Circuits, Through Hole, Right-Angle, Shrouded, 0.76µm Gold (Au) Plated, 3.00mm Tail Length, with Peg, with Pick-and-Place Polyimide Tape, Tube, Lead-Free
Application	Board-to-Board, Signal
Comments	4.3 Amps per Pole with only 1 contact powered up; 1.4 Amps per Pole with max contacts powered up
Component Type	PCB Header, Plug
Product Name	Slim-Grid
UPC	889056922371

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.4A
Voltage - Maximum	125V AC

Physical

Obsolete

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	500
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.380/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	3.00mm
PC Tail Length	3.00mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Through Hole

Obsolete

Solder Process Data

Max-Duration	10

Downloaded from Arrow.com.

Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Slim-Grid Vertical Receptacles	78120

This document was generated on Apr 12, 2026

Obsolete

Downloaded from Arrow.com.