




REV. 0

DCO 142339

COIL: @ 25°C
 RESISTANCE _____ 1350 OHMS $\pm$ 10%
 NOMINAL VOLTAGE _____ 26.5 VDC
 MUST OPERATE _____ 13.5 VDC


MUST RELEASE _____ 8.1 VDC MAX, 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: OPERATE & RELEASE 4 MS. MAX.
 CONTACT STABILIZATION TIME 2.5 MS. MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
 2 AMPS 28 VDC RESISTIVE
 50,000 OPERATIONS

DR. PBB 9/13/00 CK.TLG 9-13-00



COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. _____ QPL
 CUST. NO. M39016/13-078P REV. _____

3SBC RELAY

3SBC2023A2