



Representative Image

Catalog No. TY24M-2

Description: CABLE TIE 40LB 5.5IN RED NYLON

UPC No 786210844763

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 137mm (5.4 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 178 Newtons (40 Pounds), Military Specified (MIL-SPEC MS3367-5-2), Bulk Pack

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Red
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds , 178 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

Dimensions

Width	0.14 in , 3.6 mm
Length	5.4 in , 137 mm
Thickness	0.04 in , 1.0 mm
Bundle Diameter	0.08 to 1.38 in , 2 to 35 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant

ETIM Classification

ETIM	EC000046 Cable tie
Band width	3.6 mm

by ABB

ETIM	EC000046 Cable tie
Band width	0.14 inch
Length belt/tape/tie	137 mm
Length belt/tape/tie	5.4 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	35 mm
Max. bundle diameter	1.38 inch
Min. holding force	178 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Red
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y