

**Part Number :** [2132272630](#)

**Product Description :** 1.50mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Dual Row, Surface Mount, Vertical, 0.38µm Gold (Au) Plating, 26 Circuits, Natural

**Series Number :** 213227

**Status :** Active

**Product Category :** PCB Headers and Receptacles

---

## Documents and Resources

### Drawings

[2132272630 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[2132272630.dxf](#)

### Specifications

[2132279200-SPK-200.pdf](#)


[5031491002-PS-000.pdf](#)

[5031490002-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Compliant with Exemption 44; 34; 33   |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)7771-  |

|         |                           |
|---------|---------------------------|
|         | DC (04 Feb 2026)          |
| EU RoHS | Compliant per EU 2015/863 |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

|                |  |
|----------------|--|
| Status         | Active   |
| Category       | PCB Headers and Receptacles  |
| Series         | 213227   |
| Description    | 1.50mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Dual Row, Surface Mount, Vertical, 0.38µm Gold (Au) Plating, 26 Circuits, Natural |
| Application    | Signal, Wire-to-Board  |
| Component Type | PCB Receptacle   |
| Product Name   | CLIK-Mate  |
| UPC            | 193264243686   |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 2.0A |
|-------------------------------|------|

|                   |                  |
|-------------------|------------------|
| Voltage - Maximum | 100V AC (RMS)/DC |
|-------------------|------------------|

## Physical

|                                |                       |
|--------------------------------|-----------------------|
| Circuits (Loaded)              | 26                    |
| Circuits (maximum)             | 26                    |
| Color - Resin                  | Natural               |
| Durability (mating cycles max) | 30                    |
| First Mate / Last Break        | No                    |
| Glow-Wire Capable              | No                    |
| Guide to Mating Part           | Yes                   |
| Keying to Mating Part          | Yes                   |
| Lock to Mating Part            | Yes                   |
| Material - Metal               | Copper Alloy          |
| Material - Plating Mating      | Gold                  |
| Material - Plating Termination | Tin                   |
| Material - Resin               | Polyamide (PA)        |
| Number of Rows                 | 2                     |
| Orientation                    | Vertical              |
| Packaging Type                 | Embossed Tape on Reel |
| PCB Locator                    | No                    |
| PCB Retention                  | Yes                   |
| Pitch - Mating Interface       | 1.50mm                |
| Pitch - Termination Interface  | 1.50mm                |
| Plating min - Mating           | 0.381µm               |
| Plating min - Termination      | 0.381µm               |
| Polarized to Mating Part       | Yes                   |
| Polarized to PCB               | No                    |
| Stackable                      | No                    |
| Temperature Range - Operating  | -40° to +105°C        |
| Termination Interface Style    | Surface Mount         |

---

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|-------------|-------------|
|-------------|-------------|

|  |               |
|--|---------------|
| 1.50mm Pitch CLIK-Mate Dual<br>Row Plug Housings | <u>503149</u> |
|--|---------------|

---

This document was generated on May 04, 2026