

Downloaded from Arrow.com.

Customer Information Sheet

DRAWING No.: M80-328 TO M80-329 SHEET 2 OF 2	IF IN DOUBT - ASK	©	NOT TO SCALE	THIRD ANGLE PROJECTION	ALL DIMENSIONS IN mm

SPECIFICATIONS:
MATERIALS:
BODY = COPPER ALLOY
LATCHING COLLAR = BERYLLIUM COPPER
FINISH:
BODY = GOLD
LATCHING COLLAR = NICKEL
ELECTRICAL:
CONTACT RESISTANCE = 6mΩ MAX
CURRENT RATING = SEE TABLE (CABLE DEPENDENT)
MECHANICAL:
DURABILITY = 500 OPERATIONS
INSERTION FORCE = 8N MAX
WITHDRAWAL FORCE = 0.5N MIN
CONTACT REPLACEMENT IN INSULATOR = 5 TIMES
ENVIRONMENTAL:
TEMPERATURE RANGE = -55°C TO +125°C





NOTES:
1. CONTACT COMES SUPPLIED ASSEMBLED.
2. STRIP WIRE BY 5.0mm FOR CRIMPING.
3. CONTACT EXTRACTION TOOL = Z80-290.
4. RECOMMENDED CRIMP TOOL = Z80-294 AND POSITIONER Z80-295.
5. FOR ALL OTHER ELECTRICAL/MECHANICAL REQUIREMENTS, SEE COMPONENT SPECIFICATION C005XX (LATEST ISSUE).

PART No.	DIM 'A'	DIM 'B'	WIRE SIZE	CURRENT RATING
M80-328	Ø1.35	Ø1.85	18 AWG	8A
M80-329	Ø1.10	Ø1.65	20 AWG	5A

MGP	3	04.01.13	11898
NAME	ISS.	DATE	C/NOTE
APPROVED: MGP			
CHECKED: SB			
DRAWN: R.ADDE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL: SEE ABOVE
FINISH:
S/AREA: mm²

TITLE: DATAMATE MIX-TEK POWER CONTACT FEMALE STRAIGHT SOLDER OR CRIMP

DRAWING NUMBER: M80-328 TO M80-329

SHT 2 OF 2