

# Type C2Q

## Surface Mount Very Fast-Acting Chip Fuse

HF  C2Q Series – 0603 Size

RoHS Compliant

### Features

- Fast-acting
- Small size, 0603 SMD
- Current rating from 250mA to 5A
- Wide operating temperature range from -55°C to 125°C
- Tape and Reel for automatic SMD placement
- Compatible with 260°C IR Pb-free and wave soldering process
- Full compliance with EU Directive 2011/65/EU and amending directive 2015/863 (MSL = 1)
- Halogen Free and Lead Free
- AEC-Q Compliant
- Meets Bel automotive qualification\*
- \* - Largely based on internal AEC-Q test plan



### Applications

- Notebook
- LCD monitor
- PC computer
- Office electronic equipment
- Industrial equipment
- Medical equipment
- POE, POE+
- LCD / LED monitor
- Power supply
- LCD / LED TV
- DC-DC Converter

UK  
CA c  CE  
AEC-Q Compliant

LEAD FREE =   
HALOGEN FREE = 

### Electrical Characteristics (UL STD.248-14)

| Testing Current | Blow Time |         |
|-----------------|-----------|---------|
|                 | Minimum   | Maximum |
| 100%            | 4 Hrs.    | N/A     |
| 200%            | N/A       | 5 Sec   |
| 300%            | N/A       | 0.2 Sec |

### Safety Agency Approvals

| Safety Agency                                                                       | Safety Agency Certificate | Ampere Rating/<br>Voltage Rating | Ampere Range / Volt<br>@ I.R. ability* |
|-------------------------------------------------------------------------------------|---------------------------|----------------------------------|----------------------------------------|
|  | E506667                   | 250mA-4A/32V AC<br>63V DC        | 250mA-4A/32V AC @ 35A<br>63V DC @ 50A  |
|                                                                                     |                           | 5A / 32V AC & DC                 | 5A / 32V AC & DC @ 50A                 |


\*I.R.= Interrupting Rating = Short Circuit Rating(Amps)

### Physical Specifications


|           |                                                                                                                                                                                                                                                                                                          |
|-----------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Materials | Body : Ceramic Substrate                                                                                                                                                                                                                                                                                 |
|           | Terminations : Ag / Ni / Sn (100% Lead-free)                                                                                                                                                                                                                                                             |
|           | Element Cover Coating : Lead-free Glass                                                                                                                                                                                                                                                                  |
| Marking   | On Fuse :                                                                                                                                                                                                                                                                                                |
|           | None                                                                                                                                                                                                                                                                                                     |
|           | On Label :                                                                                                                                                                                                                                                                                               |
|           | "bel", "C2Q", "Current Rating", "Voltage Rating", "Interrupting Rating", "Appropriate Safety Logos" and   "(China RoHS compliant). |

# Type C2Q

Temperature Derating Curve



Average Time Current Curve



Electrical Specifications

| Catalog Number | Ampere Rating (A) | Nominal Cold Resistance (ohms) | Nominal Volt-drop @100% In (Volt) | Voltage and Interrupting Ratings                                                        | Nominal Melting I <sup>2</sup> T @10 In (A <sup>2</sup> Sec) | Nominal Power Dissipation @100% In (W) | Agency Approvals                                                                      |
|----------------|-------------------|--------------------------------|-----------------------------------|-----------------------------------------------------------------------------------------|--------------------------------------------------------------|----------------------------------------|---------------------------------------------------------------------------------------|
|                |                   |                                |                                   |                                                                                         |                                                              |                                        |  |
| C2Q 250        | 250mA             | 0.77                           | 0.243                             | See Table of Safety Approvals on Page 1 for Voltage and associated Interrupting Ratings | 0.00001                                                      | 0.06                                   | Y                                                                                     |
| C2Q 300        | 300mA             | 0.54                           | 0.217                             |                                                                                         | 0.00003                                                      | 0.07                                   | Y                                                                                     |
| C2Q 375        | 375mA             | 0.42                           | 0.196                             |                                                                                         | 0.00004                                                      | 0.07                                   | Y                                                                                     |
| C2Q 500        | 500mA             | 0.28                           | 0.171                             |                                                                                         | 0.00015                                                      | 0.09                                   | Y                                                                                     |
| C2Q 750        | 750mA             | 0.17                           | 0.159                             |                                                                                         | 0.0005                                                       | 0.12                                   | Y                                                                                     |
| C2Q 1          | 1A                | 0.122                          | 0.154                             |                                                                                         | 0.0010                                                       | 0.15                                   | Y                                                                                     |
| C2Q 1.25       | 1.25A             | 0.092                          | 0.152                             |                                                                                         | 0.0018                                                       | 0.19                                   | Y                                                                                     |
| C2Q 1.5        | 1.5A              | 0.073                          | 0.146                             |                                                                                         | 0.0025                                                       | 0.22                                   | Y                                                                                     |
| C2Q 1.75       | 1.75A             | 0.063                          | 0.144                             |                                                                                         | 0.0044                                                       | 0.25                                   | Y                                                                                     |
| C2Q 2          | 2A                | 0.053                          | 0.133                             |                                                                                         | 0.0063                                                       | 0.27                                   | Y                                                                                     |
| C2Q 2.5        | 2.5A              | 0.042                          | 0.130                             |                                                                                         | 0.0074                                                       | 0.33                                   | Y                                                                                     |
| C2Q 3          | 3A                | 0.034                          | 0.130                             |                                                                                         | 0.018                                                        | 0.39                                   | Y                                                                                     |
| C2Q 3.5        | 3.5A              | 0.028                          | 0.131                             |                                                                                         | 0.021                                                        | 0.46                                   | Y                                                                                     |
| C2Q 4          | 4A                | 0.023                          | 0.131                             |                                                                                         | 0.042                                                        | 0.52                                   | Y                                                                                     |
| C2Q 5          | 5A                | 0.019                          | 0.131                             |                                                                                         | 0.055                                                        | 0.66                                   | Y                                                                                     |

Consult manufacturer for other ratings

Environmental Specifications



Specifications subject to change without notice


Bel Fuse Inc.  
300 Executive Drive, Suite 300  
West Orange, NJ 07052 USA

+1 201.432.0463  
Bel.US.CS@belf.com  
[belfuse.com/circuit-protection](http://belfuse.com/circuit-protection)


|                             |                                                                                                                                                   |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Shock Resistance            | MIL-STD-202G, Method 213B, Test Condition 1<br>(100 G's peak for 6 milliseconds; Sawtooth waveform)                                               |
| Vibration Resistance        | MIL-STD-202G, Method 201A (10-55 Hz, 0.06 inch, total excursion).                                                                                 |
| Salt Spray Resistance       | MIL-STD-202G, Method 101E, Test Condition B (48 hrs.).                                                                                            |
| Insulation Resistance       | MIL-STD-202G, Method 302, Test Condition A<br>(After Opening) 10,000 ohms minimum.                                                                |
| Solderability               | MIL-STD-202G, Method 208H                                                                                                                         |
| Resistance to solder Heat   | MIL-STD-202G, Method 210F, Test Condition C. Top Side (260°C, 20 sec)<br>MIL-STD-202G, Method 210F, Test Condition D. Bottom Side (260°C, 10 sec) |
| Thermal Shock               | MIL-STD-202G, Method 107G, Test Condition B (-65°C to +125°C).                                                                                    |
| Operating Temperature       | -55°C to +125°C                                                                                                                                   |
| Moisture Sensitivity Level  | 1 (According to IPC J-Std-020)                                                                                                                    |
| Board flex(SMD)             | AEC-Q200-005                                                                                                                                      |
| Terminal strength           | AEC-Q200-006                                                                                                                                      |
| Electrical characterization | 3 temperature electrical                                                                                                                          |

## Soldering Parameters

| IR Reflow Profile (IPC/JEDEC J-STD-020D)                                                        |                 |
|-------------------------------------------------------------------------------------------------|-----------------|
| <b>Preheat &amp; Soak</b>                                                                       |                 |
| Temperature min (T <sub>min</sub> )                                                             | 150°C           |
| Temperature max (T <sub>max</sub> )                                                             | 200°C           |
| Time (T <sub>min</sub> to T <sub>max</sub> ) (t <sub>s</sub> )                                  | 60-120 seconds  |
| Average ramp-up rate (T <sub>max</sub> to T <sub>p</sub> )                                      | 3°C/second max. |
| Liquidous temperature (T <sub>L</sub> )                                                         | 217°C           |
| Time at liquidous (t <sub>L</sub> )                                                             | 60-150 seconds  |
| Peak temperature (T <sub>p</sub> )                                                              | 260°C max       |
| Time (t <sub>p</sub> ) within 5°C of the specified classification temperature (T <sub>c</sub> ) | 30 seconds      |
| Average ramp-down rate (T <sub>p</sub> to T <sub>max</sub> )                                    | 6°C/second max. |
| Time 25°C to peak temperature                                                                   | 8 minutes max.  |




| Lead-free Wave Soldering Profile                   |                                              |           |                |
|----------------------------------------------------|----------------------------------------------|-----------|----------------|
| Wave Soldering Parameter                           |                                              |           |                |
| Average ramp-up rate                               | 200°C / second                               |           |                |
| Heating rate during preheat                        | typical 1 - 2°C / second<br>Max 4°C / second |           |                |
| Final preheat temperature                          | within 125°C of soldering temperature        |           |                |
| Peak temperature Tp                                | 260°C                                        |           |                |
| Time within +0°C / -5°C of actual peak temperature | 10 seconds                                   |           |                |
| Ramp-down rate                                     | 5°C / second max.                            |           |                |
| Fraction                                           | Decimal                                      | Milliamps | Bel FGNO[XXXX] |




# Type C2Q

|      |       |     |      |  |       |      |      |
|------|-------|-----|------|--|-------|------|------|
| 1/4  | 0.250 | 250 | 0250 |  | 1.0   | 1    | 1000 |
| 3/10 | .300  | 300 | 0300 |  | 1-1/4 | 1.25 | 1250 |
| 3/8  | .375  | 375 | 0375 |  | 1-1/2 | 1.50 | 1500 |
| 1/2  | .500  | 500 | 0500 |  |       | 1.75 | 1750 |
| 3/4  | .750  | 750 | 0750 |  |       | 2.0  | 2000 |
|      |       |     |      |  | 2-1/2 | 2.5  | 2500 |
|      |       |     |      |  |       | 3.0  | 3000 |
|      |       |     |      |  | 3-1/2 | 3.5  | 3500 |
|      |       |     |      |  |       | 4.0  | 4000 |
|      |       |     |      |  |       | 5.0  | 5000 |

## Mechanical Dimensions



## Ordering Information



## Packaging

| Packaging Tape & Reel                      | Packaging Specification | Quantity | Quantity & Packaging Code |
|--------------------------------------------|-------------------------|----------|---------------------------|
| 8 mm wide tape with 7 inches Diameter reel | EIA Standard 481-E      | 5000     | 0686-XXXX-01              |