
# TSB100003DS Product Details



TSB100003DS
(3-1437387-9)
TE Internal Number: 3-1437387-9
Superseded
Search for Replacement Parts

## Europa Terminal Blocks

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

**Product Highlights:**

- 12.00 mm Centerline
- Number of Circuits = 3
- Wire Range = 0.30-6.00² [22-10] mm [AWG]
- With Wire Protection
- Integrated Fuse = No

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

**Quick Links**

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

## Documentation & Additional Information

**Product Drawings:**
- None Available

**Catalog Pages/Data Sheets:**
- None Available

**Product Specifications:**
- None Available

**Application Specifications:**
- None Available

**Instruction Sheets:**
- None Available

**CAD Files:**
- None Available

**Additional Information:**
- Product Line Information

**Related Products:**
- Tooling

## Product Features (Please use the Product Drawing for all design activity)

**Product Type Features:**
- Number of Circuits = 3
- Integrated Fuse = No
- Color = Natural
- Screw Size = M3.5
- Screw Material = Steel
- CSA File Number = LR28387
- UL File Number = E60677

**Mechanical Attachment:**
- Screw Plating = Bright Zinc/Chrome

**Electrical Characteristics:**
- Current Rating (A) = 40
- Voltage Rating (VAC) = 250
- Wire Protector Material = Stainless Steel

**Body Related Features:**
- Centerline (mm [in]) = 12.00 [0.472]
- Wire Range (mm [AWG]) = 0.30-6.00² [22-10]
- Wire Protection = With
- Ground = Without
- Series = TSB1000

**Contact Related Features:**
- Contact Base Material = Brass
- Contact Plating, Mating Area, Material = Tin

**Housing Related Features:**
- Housing Material = Polyamide - GF
- UL Flammability Rating = UL 94V-2

**Industry Standards:**
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

**Conditions for Usage:**
- Temperature Range (°C) = 100

**Other:**
- Brand = Buchanan

BOOKMARK



© 2010 Tyco Electronics All Rights Reserved | Privacy Policy



Downloaded from Arrow.com.