

Part Number : [1200860386](#)

Product Description : Nano-Change (M8) Single-Ended Cordset, 5 Poles, B-Coded, Female (90°) to Pigtail, 24 AWG, PUR Cable, 2.0m (6.56') Length

Series Number : 120086

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : 405001B09M020



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset, 5 Poles, B-Coded, Female (90°) to Pigtail, 24 AWG, PUR Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	78678833001

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Cable Diameter	5.08mm (.200")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	TPE
Material - Contact	Copper Alloy

Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	95.200/g
Orientation	90° to Pigtail
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	E152210
Wire Size (AWG)	24

This document was generated on Sep 14, 2025