

EPIC® H-A 3 TG

Innovative metal and plastic housing design

The hood made of robust plastic has a direct cable entry and pivots for a single lever. It is suitable for use in electronic laboratories.

Info

Lightweight, chemically resistant plastic housing

Protection rating UL50E tested



Waterproof



Robust



Mechanical resistance



Industrial machinery and plant engineering

Benefits

Housing in plastic or metal version. For power supply in the smallest possible space

Application range

Machine and equipment manufacturing

Control engineering

Electronic laboratory

Last Update (07.12.2016)

©2016 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-A 3 TG

Product features

Hood
Bolts for single lever
Straight cable entry
Versions with / without cable gland

Technical Data

Classification:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Material:	Housing: grey thermoplastic, black Lever: zinc-plated steel
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs are not to scale and do not represent detailed images of the respective products.

* Prices are net prices without VAT and surcharges. Sale to business customers.



EPIC® H-A 3 TG

Article number	Article description	PG	Material	Colour
10425500	H-A 3 Tgv	11	Thermoplastic	black
10426000	H-A 3 Tgv	11	Thermoplastic	grey
10426700	H-A 3 Tgv	11	Thermoplastic	black
10426400	H-A 3 Tgv	11	Thermoplastic	grey
19425500	H-A 3 Tgv M20	20	Thermoplastic	black
19426000	H-A 3 Tgv M20	20	Thermoplastic	grey

Last Update (07.12.2016)

©2016 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-A 3 TG

