

Specification Sheet

Part Number: 155-30602



Design gives quick and easy assembly by hand without the need for tools.

Mount can be used in a wide variety of applications where 5mm weld studs or 5mm ISO bolts.

Design provides low insertion force and high extraction force.

Standoff Stud Mount Tie, 5.0 mm studs, 6.0" Long, PA66HS, Black, 500/pkg

Article Number 155-30602

Type T50SSBS5OT-E

Color Black (BK)

Quantity Per bag

Product Description The Standoff Stud Mount tie applies easily to weld studs and secures bundles away from fixing holes. These are used primarily in the automotive industry, but can be used in a variety of applications.

Short Description Standoff Stud Mount Tie, 5.0 mm studs, 6.0" Long, PA66HS, Black, 500/pkg

Global Part Name T50SSBS5OT-E-PA66HS-BK

Minimum Tensile Strength (Imperial)	45.0
Minimum Tensile Strength (Metric)	200
Length L (Imperial)	6.3
Length L (Metric)	160.0
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05

Thickness T (Metric)	1.35
Stud Length Max (Imperial)	0.65
Stud Length Max (Metric)	16.5
Stud Diameter (Metric)	5.0 mm
Stud Diameter (Imperial)	0.2
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)