
N-Channel 20 V (D-S) MOSFET

SOT-23 (TO-236)



Top View

Marking code: C7

FEATURES

- TrenchFET® power MOSFET
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


Pb-free

RoHS COMPLIANT

HALOGEN FREE Available

APPLICATIONS

- Load switching for portable devices
- DC/DC converter



N-Channel MOSFET

PRODUCT SUMMARY	
V_{DS} (V)	20
$R_{DS(on)}$ max. (Ω) at V_{GS} = 4.5 V	0.057
$R_{DS(on)}$ max. (Ω) at V_{GS} = 2.5 V	0.075
Q_g typ. (nC)	3.5
I_D (A)	2.9
Configuration	Single

ORDERING INFORMATION	
Package	SOT-23 (TO-236)
Lead (Pb)-free and halogen-free	Si2302HDS-T1-GE3

ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C, unless otherwise noted)

PARAMETER		SYMBOL	5 S	STEADY STATE	UNIT
Drain-source voltage		V_{DS}	20	20	V
Gate-source voltage		V_{GS}	± 8	± 8	
Continuous drain current (T_J = 150 °C) [a]	T_A = 25 °C	I_D	2.9	2.6	A
	T_A = 70 °C		2.3	2.1	
Pulsed drain current [b]		I_{DM}	10	10	
Continuous source current (diode conduction) [a]		I_S	0.72	0.6	
Power dissipation [a]	T_A = 25 °C	P_D	0.86	0.71	W
	T_A = 70 °C		0.55	0.46	
Operating junction and storage temperature range		T_J, T_{stg}	-55 to +150	-55 to +150	°C

THERMAL RESISTANCE RATINGS

PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT
Maximum junction-to-ambient [a]	t ≤ 5 s	R_{thJA}	120	145	°C/W
	Steady state		140	175	
Maximum junction-to-foot	Steady state	R_{thJF}	62	78	

Notes

a. Surface mounted on 1" x 1" FR4 board

b. Pulse width limited by maximum junction temperature

For technical questions, contact: pmostechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

SPECIFICATIONS (T_A = 25 °C, unless otherwise noted)						
PARAMETER	**SYMBOL**	**TEST CONDITIONS**	**LIMITS**			**UNIT**
			MIN.	**TYP.**	**MAX.**	
Static						
Drain-source breakdown voltage	V_{DS}	V_{GS} = 0 V, I_D = 250 µA	20	-	-	V
Gate-threshold voltage	$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250 µA	0.40	-	0.85	
Gate-body leakage	I_{GSS}	V_{DS} = 0 V, V_{GS} = ± 8 V	-	-	± 100	nA
Zero gate voltage drain current	I_{DSS}	V_{DS} = 20 V, V_{GS} = 0 V	-	-	0.1	µA
		V_{DS} = 20 V, V_{GS} = 0 V, T_J = 50 °C	-	-	4	
		V_{DS} = 20 V, V_{GS} = 0 V, T_J = 70 °C	-	-	15	
On-state drain current [a]	$I_{D(on)}$	V_{DS} ≥ 10 V, V_{GS} = 4.5 V	6	-	-	A
Drain-source on-resistance [a]	$R_{DS(on)}$	V_{GS} = 4.5 V, I_D = 3.6 A	-	0.045	0.057	Ω
		V_{GS} = 2.5 V, I_D = 3.1 A	-	0.056	0.075	
Forward transconductance [a]	g_{fs}	V_{DS} = 5 V, I_D = 3.6 A	-	13	-	S
Diode forward voltage	V_{SD}	I_S = 0.95 A, V_{GS} = 0 V	-	0.7	1.2	V
Dynamic [b]						
Total gate charge	Q_g	V_{DS} = 10 V, V_{GS} = 4.5 V, I_D = 3.6 A	-	3.5	5.5	nC
Gate-source charge	Q_{gs}		-	0.6	-	
Gate-drain charge	Q_{gd}		-	0.45	-	
Gate resistance	R_g	f = 1 MHz	2	4	8	Ω
Switching						
Turn-on delay time	$t_{d(on)}$	V_{DD} = 10 V, R_L = 2.78 Ω I_D ≅ 3.6 A, V_{GEN} = 4.5 V, R_g = 1 Ω	-	8	15	ns
Rise time	t_r		-	7	15	
Turn-off delay time	$t_{d(off)}$		-	30	45	
Fall time	t_f		-	7	15	
Source-drain reverse recovery time	t_{rr}	I_F = 3.6 A, di/dt = 100 A/µs	-	8.5	15	
Body diode reverse recovery charge	Q_{rr}		-	2	4	nC

Notes

a. Pulse test: Pulse width ≤ 300 µs, duty cycle ≤ 2 %

b. Guaranteed by design, not subject to production testing


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

For technical questions, contact: pmostechsupport@vishay.com


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




Transfer Characteristics



On-Resistance vs. Drain Current




Capacitance




Gate Charge

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




On-Resistance vs. Junction Temperature




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage



Single Pulse Power




Safe Operating Area, Junction-to-Ambient

For technical questions, contact: pmostechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Normalized Thermal Transient Impedance, Junction-to-Ambient

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?61627.

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.


SOT-23 (TO-236): 3-LEAD



Dim	MILLIMETERS		INCHES	
	Min	Max	Min	Max
A	0.89	1.12	0.035	0.044
A_1	0.01	0.10	0.0004	0.004
A_2	0.88	1.02	0.0346	0.040
b	0.35	0.50	0.014	0.020
c	0.085	0.18	0.003	0.007
D	2.80	3.04	0.110	0.120
E	2.10	2.64	0.083	0.104
E_1	1.20	1.40	0.047	0.055
e	0.95 BSC		0.0374 Ref	
e_1	1.90 BSC		0.0748 Ref	
L	0.40	0.60	0.016	0.024
L_1	0.64 Ref		0.025 Ref	
S	0.50 Ref		0.020 Ref	
q	3°	8°	3°	8°
ECN: S-03946-Rev. K, 09-Jul-01 DWG: 5479				

Downloaded from Arrow.com.

RECOMMENDED MINIMUM PADS FOR SOT-23



Recommended Minimum Pads
Dimensions in Inches/(mm)

Return to Index

APPLICATION NOTE

Downloaded from Arrow.com.

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2026 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.