
SIGN	DATE	DESCRIPTION	APPROVER
1	03/23'09	modify specification	Jacke
2	2009.09.18	The design is changed	Jacke
3	2009.12.25	The Material is changed from PhBz to Copper	Jacke
4	2012.09.07	Added TUV standard	Chen Bo
5	2013.11.08	Added the product description	Chen Bo
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	



E T xx 0 2 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
:
16: 16 POLES


COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)


G RoHS compliant (lead<4%) In copper Alloy
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

Any special item by customer requst. please contact sales department.

Material:
- Item ⓐ Terminal(housing): Thermoplastic (UL94V-0)
- Item ⓑ Terminal(cover): Thermoplastic (UL94V-0)
- Item ⓒ Clamp: Brass Ni plated
- 3 Item ⓓ Female contact : Copper. Tin plated
- Item ⓔ Wire guard: Stainless steel
- Item ⓕ Terminal Screw: Steel , zinc plating "*" slot type

1 Electrical:	cULus	TUV
Voltage rating:	300 V	800V
Current rating:	32 A	32A
Wire range:		0.2-6mm²
Solid wire(AWG):	8-24	
Stranded wire(AWG):	8-24	
Torque:	7 LB-In	0.8N.m
Screw:	M3.5	
Wire strip length:	10-11 mm	
Withstanding Voltage:	1.6KV	6KV
Operating temperature:	-40°C to +115°C	
4 Safety Approval:	c UL us	TÜV
Critical dimension:	C	





DIM		TOL			
		2P-4P	5P-8P	9P-12P	13P-16P
Dim L	N×7.62	±0.15	±0.20	±0.30	±0.40
Dim P	(N-1)×7.62	±0.15	±0.20	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	ET-7.62 Series (Without Flange) "*" (Match VC series) 5				
PART NO.	ETxx02x0xxxxG			DWG NO.	8ET0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Chen Bo 11/08`13	Chen Bo 11/08`13	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: G	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°

Downloaded from Arrow.com.