

UZG3.95mmLmax. Chip Type,
Wide Temperature Range

- Chip type with 3.95mmLmax height. Operating over wide temperature range of -40 to +105°C.
- Designed for surface mounting on high density PC board.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU, (EU)2015/863).
- AEC-Q200 Qualified. Please contact us for details.


**UZG**

Specifications


Item	Performance Characteristics							
Category Temperature Range	-40 to +105°C							
Rated Voltage Range	6.3 to 50V							
Rated Capacitance Range	1 to 100μF							
Capacitance Tolerance	±20% at 120Hz, 20°C							
Leakage Current ※	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01 CV or 3 (μA) , whichever is greater.							
Tangent of loss angle (tan δ)	Rated voltage (V)	6.3	10	16	25	35	50	120Hz 20°C
	tan δ (max.)	0.38	0.32	0.20	0.16	0.14	0.14	
Stability at Low Temperature	Rated voltage (V)	6.3	10	16	25	35	50	120Hz
	Impedance ratio Z(-25°C) / Z(+20°C)	6	5	3	3	3	3	
	ZT / Z20 (max.) Z(-40°C) / Z(+20°C)	10	10	6	6	4	4	
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 105°C.				Capacitance change		Within ±30% of the initial capacitance value	
					tan δ		300% or less than the initial specified value	
					Leakage current		Less than or equal to the initial specified value	
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.							
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C. The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C.				Capacitance change		Within ±10% of the initial capacitance value	
					tan δ		Less than or equal to the initial specified value	
					Leakage current		Less than or equal to the initial specified value	
Marking	Black print on the case top.							

※ I : Leakage Current (μA), C : Rated Capacitance (μF), V : Rated Voltage (V)

Chip Type



Type numbering system (Example : 16V 10μF)



Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

● Dimension table in next page.

UZG

■ Dimensions

Rated Voltage (V) (code)	Rated Capacitance (μ F)	Case Size ϕ D \times L (mm)	$\tan \delta$	Leakage Current (μ A) (at 20°C after 2 minutes)	Rated Ripple (mA _{rms}) (105°C/120Hz)	Part Number
6.3 (0J)	22	4 \times 3.9	0.38	3	19	UZG0J220MCL1GB
	33	5 \times 3.9	0.38	3	26	UZG0J330MCL1GB
	47	5 \times 3.9	0.38	3	32	UZG0J470MCL1GB
	100	6.3 \times 3.9	0.38	6.3	52	UZG0J101MCL1GB
10 (1A)	22	5 \times 3.9	0.32	3	24	UZG1A220MCL1GB
	33	5 \times 3.9	0.32	3.3	30	UZG1A330MCL1GB
	47	6.3 \times 3.9	0.32	4.7	40	UZG1A470MCL1GB
16 (1C)	10	4 \times 3.9	0.20	3	16	UZG1C100MCL1GB
	22	5 \times 3.9	0.20	3.52	26	UZG1C220MCL1GB
	33	6.3 \times 3.9	0.20	5.28	35	UZG1C330MCL1GB
	47	6.3 \times 3.9	0.20	7.52	44	UZG1C470MCL1GB
25 (1E)	4.7	4 \times 3.9	0.16	3	11	UZG1E4R7MCL1GB
	10	5 \times 3.9	0.16	3	20	UZG1E100MCL1GB
	22	6.3 \times 3.9	0.16	5.5	33	UZG1E220MCL1GB
	33	6.3 \times 3.9	0.16	8.25	42	UZG1E330MCL1GB
35 (1V)	4.7	4 \times 3.9	0.14	3	13	UZG1V4R7MCL1GB
	10	5 \times 3.9	0.14	3.5	22	UZG1V100MCL1GB
	22	6.3 \times 3.9	0.14	7.7	36	UZG1V220MCL1GB
50 (1H)	1	4 \times 3.9	0.14	3	5.4	UZG1H010MCL1GB
	2.2	4 \times 3.9	0.14	3	9.6	UZG1H2R2MCL1GB
	3.3	4 \times 3.9	0.14	3	12	UZG1H3R3MCL1GB
	4.7	5 \times 3.9	0.14	3	16	UZG1H4R7MCL1GB
	10	6.3 \times 3.9	0.14	5	26	UZG1H100MCL1GB

- For taping specifications, recommended land size/soldering by reflow and minimum order quantity, please refer to the Guidelines for Aluminum Electrolytic Capacitors.