





PRODUCT NUMBER	PITCH
V7xx12x000J0G	3.50 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item@ Terminal body:Thermoplastic (UL94V-0)
- Itemⓓ Female contact:PhBz(CuSn),Tin plated
- ItemⒸ With Flange Nut :Brass M2.5

Electrical cULus

- Voltage rating: 300V AC
- Current rating: 4A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:

N = Number of poles
Dim B=(N-1)×3.5
Dim C=(N-1)×3.5+14.2
Dim D=(N-1)×3.5+8.6
Dim E=(N-1)×3.5

poles	Tolerance
2-5p	±0.10
6-10p	±0.15
11-15p	±0.20
16-20p	±0.25
21-24p	±0.30

PART NO.: V7 xx 12 x 0 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
02	2poles	0 Black (RAL9005)	
03	3poles	2 Red (RAL3001/D)	
...	...	3 Orange(RAL2011/P)	
24	24poles	4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5✓	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK	
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title TERMINAL BLOCK	
				angles	X.±0.5		PLUGGABLE PCB PLUG, WITH FLANGE, VERTICAL	
				flatness	X.X±0.3		dwg no	
				total runout	X.XX±0.1		sheet 1 of 1 size	
				dr	EVIN ZHONG 043014		V7xx12x000J0G	
				enrg	EVIN ZHONG 043014		A4	
				chr	HANKE FENG 043014		type	
				appd	SHI JUN 043014		CUSTOMER Drawing	
sheet index	revision	sheet	A					