



**Part Number :** [1300280023](#)  
**Product Description :** Micro-Change (M12)  
Double-Ended Cordset, 5 Poles, Male  
(Straight) to Female (Straight), 22 AWG, Gray  
DeviceNet Thin Stranded Cable, 0.50m (1.64')  
Length  
**Series Number :** 130028  
**Status :** Active  
**Product Category :** Circular Industrial  
Cordsets  
**Engineering Number :** DND22A-M005



Documents & Resources

Drawings  
[1300280023\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130028
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, Gray DeviceNet Thin Stranded Cable, 0.50m (1.64') Length
IP Rating	IP67
Product Name	DeviceNet, Micro-Change (M12)
Protocol	N/A
Type	Double Ended
UPC	78678801123

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

### Physical

Cable Diameter	7.24mm (.285")
Cable Length	0.50m (1.64')
Color - Cable Jacket	Gray
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None

Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Net Weight	70.623/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thin (Drop)
Wire Size (AWG)	22

---



---

This document was generated on Apr 19, 2025