



## Notes

### Safety Information

**Notice!** Live parts can be easily touched! Protection against direct contact must be provided by the equipment manufacturer, e.g., using a WAGO 709 Series Cover (see "Accessories") or a similar cover. The installation guidelines must be observed for each individual application.

### Note

Max. permissible forward current per the manufacturer's data sheet. With all diodes loaded, the continuous current must be reduced to 0.45 A.

## Electrical data

Operating voltage	≤ 250 VAC/VDC
Peak reverse voltage	1000 V
Type of diode	1N4007; with common anode
Number/type of diode/LED	14 diodes
Forward voltage per diode	1.1 V
Forward current per diode (resistive)	1 A
Leakage current	50 µA

## Safety and protection

Pollution degree	2
Protection type	IP00

## Connection data

Note (conductor cross-section)	12 AWG: THHN, THWN	Connection 1
		Connection technology
		WAGO connector
		Solid conductor
		Fine-stranded conductor
		Strip length

**Physical data**

Width	42.5 mm / 1.673 inches
Height from the surface	31.5 mm / 1.24 inches
Depth	62.5 mm / 2.461 inches

**Mechanical data**

Mounting type	Mounting on DIN-rail via DIN-rail adapter
Housing design	PCB

**Material data**

Fire load	0 MJ
Weight	25.3 g

**Environmental requirements**

Ambient temperature (operation)	-25 ... +40 °C
Ambient temperature (storage)	-40 ... +70 °C
Relative humidity	≤ 85 % (non-condensing)
Operating altitude (max.)	2000 m

**Standards and specifications**

Standards/specifications	EN 61010-2-201
--------------------------	----------------

**Commercial data**

Product Group	6 (INTERFACE ELECTRONIC)
PU (SPU)	50 (1) pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454193027
Customs tariff number	85369010000

**Product classification**

UNSPSC	39121629
eCl@ss 10.0	27-14-11-27
eCl@ss 9.0	27-14-11-49
ETIM 9.0	EC000903
ETIM 8.0	EC000903
ECCN	NO US CLASSIFICATION

**Environmental Product Compliance**

CAS-No.	7439-92-1 79-94-7
REACH Candidate List Substance	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol Lead
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	7(a) 7(c)-I 7(c)-II
SCIP notification number (Austria)	bb8a0b0e-3964-4120-8e1c-27204a68aba9
SCIP notification number (Belgium)	d29bd272-bc7c-4a8c-a541-1c0b42b14821
SCIP notification number (Bulgaria)	24f739dd-8317-45a7-8980-1510efe55520
SCIP notification number (Czech Republic)	de65635f-189e-4b60-b7b1-48b37fcbce93
SCIP notification number (Denmark)	0fc6bb6e-77af-4b34-8aea-9e6aa426b88b

## Environmental Product Compliance

SCIP notification number (Finland)	1c32d05a-fa8a-47f3-9632-b7411ac1844c
SCIP notification number (France)	3eb75477-7c50-44a0-9f9e-1eb744efccbc
SCIP notification number (Germany)	2b15fbcb-2491-4083-af0a-2e06d361f922
SCIP notification number (Hungary)	f6e7d9c9-e05b-4f92-97a3-0c8a9084acdb
SCIP notification number (Italy)	afc9c10b-6fd0-4112-9ff1-36402180ea5e
SCIP notification number (Netherlands)	e42ec1b7-00e6-4fcf-b0f1-63538a9fa38b
SCIP notification number (Poland)	d2f4ac0c-5b1c-402a-8d17-45565173e323
SCIP notification number (Romania)	2e4ea159-22f6-4859-80a8-cfcfb994f213
SCIP notification number (Sweden)	f8922ba3-ecb8-48bc-b661-796ed0b482ad

## Approvals / Certificates

### General approvals



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03084

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product  
Compliance 289-121



## Documentation

Bid Text		
289-121	11.02.2015	doc 25.00 KB
289-121	19.02.2019	xml 3.50 KB

Instruction Leaflet		
Operation and Assembly Instructions Interface	V 1.0.0 02.04.2025	pdf 1246.19 KB



## CAD/CAE-Data

CAD data		
2D/3D Models 289-121		

CAE data		
EPLAN Data Portal 289-121		
WSCAD Universe 289-121		
ZUKEN Portal 289-121		



## 1 Compatible Products

### 1.1 Required Accessories

#### 1.1.1 Installation

##### 1.1.1.1 Mounting carrier and mounting feet

**Item No.: 288-001**

Mounting carrier; gray

**Item No.: 288-002**

Universal mounting foot; snap-fit type; suitable for DIN 15, 35 and 32 rails; gray

## 1.2 Optional Accessories

### 1.2.1 Ferrule

#### 1.2.1.1 Ferrule

**Item No.: 216-301**Ferrule; Sleeve for 0.25 mm<sup>2</sup> / AWG 24; insulated; electro-tin plated; yellow**Item No.: 216-321**Ferrule; Sleeve for 0.25 mm<sup>2</sup> / AWG 24; insulated; electro-tin plated; yellow**Item No.: 216-302**Ferrule; Sleeve for 0.34 mm<sup>2</sup> / 22 AWG; insulated; electro-tin plated; light turquoise**Item No.: 216-322**Ferrule; Sleeve for 0.34 mm<sup>2</sup> / 22 AWG; insulated; electro-tin plated; light turquoise**Item No.: 216-201**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; insulated; electro-tin plated; electrolytic copper; acc. to DIN 46228, Part 4/09.90; white**Item No.: 216-241**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white**Item No.: 216-221**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; insulated; electro-tin plated; white**Item No.: 216-242**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray**Item No.: 216-262**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray**Item No.: 216-202**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; gray**Item No.: 216-222**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; gray**Item No.: 216-243**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red**Item No.: 216-263**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red**Item No.: 216-203**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; red**Item No.: 216-223**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; red**Item No.: 216-204**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; black**Item No.: 216-224**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; black**Item No.: 216-244**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black**Item No.: 216-264**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black**Item No.: 216-284**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

## 1.2.2 Installation

### 1.2.2.1 Cover



[Item No.: 709-153](#)

Cover; Type 1; suitable for cover carrier, type 1; 1 m long; transparent

### 1.2.2.2 Cover carrier



[Item No.: 709-167](#)

Cover carrier; Type 1; incl. fixing/retaining screws and knurled nut; suitable for 279 to 282 and 880 Series rail-mounted terminal blocks; suitable for 264 Series miniature rail-mounted terminal blocks; suitable for 270 Series sensor and actuator terminal blocks; gray

## 1.2.3 Marking

### 1.2.3.1 Marking strip



[Item No.: 210-831](#)

Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive; white



[Item No.: 210-832](#)

Marking strips; on reel; 3 mm wide; plain; Self-adhesive; white

## 1.2.4 Tool

### 1.2.4.1 Operating tool



[Item No.: 210-720](#)

Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured